



**Part Number :** [510670900](#)  
**Product Description :** Mighty-SPOX Wire-to-Wire and Wire-to-Board Housing, 3.50mm Pitch, Positive Lock, 9 Circuits, Natural  
**Series Number :** 51067  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources

### Drawings

- [510670900\\_sd.pdf](#)
- [SPK-51067-001-001.pdf](#)
- [SPK-51067-001-002.pdf](#)

### 3D Models and Design Files


- [510670900\\_stp.zip](#)

### Specifications

- [PS-51067-001-001.pdf](#)
- [PS-51067-002-001.pdf](#)
- [PS-51067-003-001.pdf](#)
- [PS-51067-004-001.pdf](#)
- [PS-51067-005-001.pdf](#)
- [PS-51067-006-001.pdf](#)
- [PS-51067-007-001.pdf](#)
- [PS-51067-008-001.pdf](#)
- [PS-51067-016-001.pdf](#)
- [PS-51067-017-001.pdf](#)
- [PS-51067-018-001.pdf](#)
- [PS-51067-019-001.pdf](#)
- [PS-51067-022-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

#### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Housings
Series	51067
Description	Mighty-SPOX Wire-to-Wire and Wire-to-Board Housing, 3.50mm Pitch, Positive Lock, 9 Circuits, Natural
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Mighty-SPOX
UPC	800754363501

#### Agency

CSA	LR19980
UL	E29179

#### Physical

Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle

Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	1772.800/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mighty-SPOX Plug Housings	<u>51114</u>
3.50mm Pitch Mighty-SPOX Vertical Headers	<u>53258</u>
3.50mm Pitch Mighty-SPOX Right-Angle Headers	<u>53259</u>
7.00mm Pitch Mighty-SPOX Vertical Headers	<u>53265</u>
7.00mm Pitch Mighty-SPOX Right-Angle Headers	<u>53266</u>

### Use with Part(s)

Description	Part Number
Mighty-SPOX Female Crimp Terminals	<u>50217</u>