

### FR601 - Bizflame Work Lightweight Stretch Panelled FR Jacket

**Collection:** Bizflame™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizflame Work: 99% Cotton, 1% Carbon Fibre, 210g

**Outer Carton:** 20

#### Product information

Contemporary work jacket that fits as good as it looks with innovative design features like stretch panelling provides excellent comfort and flexibility in key movement areas. Other key features include upper and lower back ventilation, multiple pockets for ample storage, adjustable cuffs and reflective trims.

#### Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

#### Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 9 CAL/CM<sup>2</sup>, ATPV 9.4 CAL/CM<sup>2</sup>)



#### Features

- Innovative stretch panelling in key movement areas provides excellent comfort and flexibility
- Protection against radiant, convective and contact heat
- Sleeve pocket
- Back vents on upper and lower back for maximum breathability
- Non-magnetic - nickel and ferrous free
- Hook and loop cuffs for a secure fit
- Sew on flame resistant industrial wash tape
- Radio loops for easy clipping of a radio
- Two-way zip for quick and easy access
- 5 pockets for ample storage
- Suitable to be worn in an ATEX environment

### FR601 - Bizflame Work Lightweight Stretch Panelled FR Jacket Commodity Code: 6203321000

#### Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
Bracetown Business Park  
D15 YN2P, Ireland  
Cert No: 2777/24392-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)  
SATRA Technology Park  
NN16 8SD, United Kingdom

#### Wash Care



#### Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR601ORRS	Orange	65.0	40.0	26.0	0.7680	0.0676	5036108353910	25036108842456
FR601ORRM	Orange	65.0	40.0	26.0	0.8030	0.0676	5036108353903	25036108842449
FR601ORRL	Orange	65.0	40.0	26.0	0.8610	0.0676	5036108353897	25036108842432
FR601ORRXL	Orange	65.0	40.0	26.0	0.8610	0.0676	5036108353927	25036108842463
FR601ORRXXL	Orange	65.0	40.0	26.0	0.9120	0.0676	5036108353934	25036108842470
FR601ORRXXXL	Orange	65.0	40.0	26.0	0.9330	0.0676	5036108353941	25036108842487