



Chemical protection

ULTRANEО 407

Prolonged contact (or immersion) | short wear

Ultra-high performance chemical protection



CHEMICAL PROTECTION
TYPE A



2111X

EN ISO 374-1



TYPE A
ABCJLMNS

EN ISO 374-5



CATEGORY 3



0334

DEXTERITY

EN420:
5/5

SPECIFIC ADVANTAGES



Productivity

- Good grip due to the embossed texture



Skin protection

- Broad chemical resistance (acids, aliphatic solvents, solvent mixtures), increased by the thickness of the material



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Practical

- Easy to pull on and off, due to chlorinated interior

INDUSTRIES

- Mechanical industry
- Chemical industry

APPLICATIONS

- Etching / degreasing
- Surface treatment of metals (acids)
- Handling and transporting drums of chemical products
- Handling on alkylation units
- Site pollution control



Chemical protection

ULTRANEО 407

Prolonged contact (or immersion) | short wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
2 1 1 1 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	A: Methanol
TYPE A	B: Acetone
	C: Acetonitrile
	J: n-Heptane
	L: Sulphuric acid 96%
	M: Nitric acid 65%
	N: Acetic acid 99%
	S: Hydrofluoric acid 40%
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Chlorinated
Exterior finish	Embossed texture
Material	Polychloroprene
Cuff characteristic	Straight cuff
Colour.s	Black
Length (cm)	36
Thickness (mm)	0.75
European sizes	9 10

LOGISTIC DETAILS

Packaging	1 pair/bag 6 pairs/bag 48 pairs/carton
-----------	--

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/10/18/2081
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France