


Product datasheet

Specifications

MOUNTING PLATE TARIF CLASS 2 INV+NSX250 WIDTH 600/650



LVS03145

EAN Code: 3606481875136

Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 + 150 mm depth 400 mm Cubicle - width 650 mm depth 400 mm
Mounting plate description	Insulating
Installed device	ComPact: fixed INV160 - control: direct front rotary handle - vertical installation ComPact: fixed INV200 - control: direct front rotary handle - vertical installation ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation ComPact: fixed INV100 - control: toggle - vertical installation ComPact: fixed INV160 - control: toggle - vertical installation ComPact: fixed INV200 - control: toggle - vertical installation ComPact: fixed INV250 - control: toggle - vertical installation
Poles description	1 x 4P: fixed INV250 vertical installation 1 x 4P: fixed INV100 vertical installation 1 x 4P: fixed INV160 vertical installation 1 x 4P: fixed INV200 vertical installation 1 x 4P: fixed NSX100...160 vertical installation 1 x 4P: fixed NSX250 vertical installation
Number of vertical modules [50 mm]	12 module(s): NSX100...160 with earth leakage protection , direct in 600 mm Widefloor-standing enclosure 12 module(s): NSX100...160 with earth leakage protection , direct in 600 mm Widewall-mounted enclosure 12 module(s): NSX250 with earth leakage protection , direct in 650 + 150 mm Widecubicle
Standards	NF C 15-100 IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)

Width	600 mm
Height	200 mm
Net weight	1.28 kg
Functional unit	600 mm PrismaSeT G floor-standing enclosure ComPact INV100 fixed toggle vertical 4P 1 direct 137.5 mm 600 mm PrismaSeT G wall-mounted enclosure ComPact INV100 fixed toggle vertical 4P 1 direct 137.5 mm 600 mm PrismaSeT G floor-standing enclosure ComPact INV160 fixed toggle vertical 4P 1 direct 125 mm 600 mm PrismaSeT G wall-mounted enclosure ComPact INV160 fixed toggle vertical 4P 1 direct 125 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 137.5 mm 600 mm PrismaSeT G floor-standing enclosure ComPact INV200 fixed toggle vertical 4P 1 direct 125 mm 600 mm PrismaSeT G wall-mounted enclosure ComPact INV200 fixed toggle vertical 4P 1 direct 125 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 137.5 mm 600 mm PrismaSeT G floor-standing enclosure ComPact INV250 fixed toggle vertical 4P 1 direct 125 mm 600 mm PrismaSeT G wall-mounted enclosure ComPact INV250 fixed toggle vertical 4P 1 direct 125 mm 600 mm PrismaSeT G floor-standing enclosure ComPact NSX100...160 with fixed toggle vertical 4P 1 direct 12 125 mm 600 mm PrismaSeT G wall-mounted enclosure ComPact NSX100...160 with fixed toggle vertical 4P 1 direct 12 125 mm 650 + 150 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with fixed toggle vertical 4P 1 direct 12 137.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	20.0 cm
Package 1 Length	47.0 cm
Package 1 Weight	1.33 kg
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	13.903 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	74.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	124.0 kg

Contractual warranty

Warranty (in months)	18
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

REACH Regulation [REACH Declaration](#)

Halogen-free status **Halogen free plastic parts product**

PVC free **Yes**

Silicone-free **Yes**

Use Longer

Lifetime extension

Repair **No**

Use Again

Repack and remanufacture

End of life manual availability **No need of specific recycling operations**

Take-back **No**