

CRIMPFOX-P CDC 2.5L - Crimping pliers



1142833

<https://www.phoenixcontact.com/in/products/1142833>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping tool, for COMBICON crimp connectors, cross section: 1.50 ... 2.50 mm², unlockable pressure lock, precise parallel crimping, front entry, incl. positioning tool

Your advantages

- The integrated positioning tool ensures that the contacts are perfectly aligned
- Precision-manufactured dies ensure consistently high levels of quality during contact processing
- Parallel motion sequences of the dies for symmetrical and optimum crimping results
- High crimping force with low manual force
- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1142833
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	BH3136
GTIN	4063151103439
Weight per piece (including packing)	509 g
Weight per piece (excluding packing)	463.9 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-P CDC 2.5L - Crimping pliers



1142833

<https://www.phoenixcontact.com/in/products/1142833>

Technical data

Product properties

Product type	Crimping tool
Compression	B crimp
Product property	Including positioning guide
	Symmetrical crimping shape due to parallel pliers movement
	Marked die stations

Crimping position 1

Max. cross section	2.5 mm ²
AWG max	14

Crimping position 2

Max. cross section	1.5 mm ²
AWG max	16

Connection data

Conductor connection

Cross section range, metric	1.5 mm ² ... 2.5 mm ²
Cross section range AWG	16 ... 14

Dimensions

Length	233 mm
--------	--------

CRIMPFOX-P CDC 2.5L - Crimping pliers

1142833

<https://www.phoenixcontact.com/in/products/1142833>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1142833>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-P CDC 2.5L - Crimping pliers

1142833

<https://www.phoenixcontact.com/in/products/1142833>



Classifications

ECLASS

ECLASS-11.0	21043811
ECLASS-12.0	21043811
ECLASS-13.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-P CDC 2.5L - Crimping pliers



1142833

<https://www.phoenixcontact.com/in/products/1142833>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CRIMPFOX-P CDC 2.5L - Crimping pliers

1142833

<https://www.phoenixcontact.com/in/products/1142833>



Accessories

CDC-MP 1,5-2,5 - Crimp contact

1016660

<https://www.phoenixcontact.com/in/products/1016660>



Crimp contact

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in