



Main

Range of product	Modicon M171/M172
Accessory / separate part category	Thermal management accessory
Accessory / separate part type	Probe

Complementary

Temperature probe type	NTC
Device mounting	Wall mounted
Mounting support	Mounting box
Output type	NTC 10 kOhm/25 °C +/- 1 °C
Product specific application	Outdoor temperature measurement
Measurement range	- 50...100 °C
Electrical connection	Screw-clamp terminals
Fixing mode	2 fixing points
Width	69 Mm
Height	75 Mm
Depth	44 Mm

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-50...100 °C
Ambient air temperature for storage	-50...100 °C

Ordering and shipping details

Category	US1PC1222537
Discount Schedule	PC12
GTIN	3606481390189
Returnability	No
Country of origin	GR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 Cm
Package 1 Width	8.9 Cm
Package 1 Length	12.1 Cm
Package 1 Weight	117.0 G
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.0 Cm
Package 2 Width	30.0 Cm
Package 2 Length	40.0 Cm
Package 2 Weight	2.58 Kg

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to cause cancer.
Total lifecycle Carbon footprint	10 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	9.8391220267
Carbon footprint of the manufacturing phase [A1 to A3]	10 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.0150956875
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.0001169145
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Mercury free	Yes
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	0.0926793657
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Total lifecycle Carbon footprint	10
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	2c365b3a-5b0a-48fd-acc7-751c89a723a2
REACH Regulation	Reference contains Substances of Very High Concern above the threshold 🔗
EU RoHS Directive	Compliant By Exemption 🔗
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never be incinerated.

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**