

PUZZI 2/1 BP

Maximum freedom of movement when removing stains down to the fibre on all types of textiles: portable, powerful 36 V cordless spray extraction machine with ergonomic upholstery nozzle.



Order no.

1.101-750.0

- 2-litre fresh water tank, excellent cleaning results for textiles, compact
- 36 V battery-powered device, powerful pump and motor technology
- Short and ergonomic upholstery nozzle, 1.9 m spray/suction hose

Technical data

EAN code		4066529097996
Battery platform		36 V battery platform
Fresh/dirty water tank	l	1.7 / 2.9
Air flow	l/s	16
Vacuum	kPa	16
Spray rate	ml/min	350
Spray pressure	MPa	0.16 - 0.22
Turbine capacity	W	350
Pump capacity	W	4
Rated input power	W	350
Sound pressure level	dB(A)	72
Nominal size of accessory		ID 30
Number of batteries required	Piece(s)	1
Run time per battery charge	min	Normal mode: 46 (7.5 Ah) / Normal mode: 37 (6.0 Ah)
Charging current	A	6
Power supply for battery charger	V / Hz	100 - 240 / 50 - 60
Colour		anthracite
Weight without accessories	kg	3.7
Weight incl. packaging	kg	5.4
Dimensions (L × W × H)	mm	410 × 235 × 250

Scope of supply

Versions: Battery and battery charger not included

spray/suction hose: 1.9 m

Short upholstery nozzle with handle

Fresh water tank

Dirty water tank


Detergents: RM 764 N / 125 ml

Equipment

Hose transport lock

Integrated accessory storage

nozzle mouthpiece: Upholstery nozzle / orange



Excellent cleaning performance

- Excellent cleaning with a clear 'before-and-after' effect.
- High vacuum for excellent suction power.
- Extremely fine and even spray pattern from the upholstery nozzle.



Compact design with high mobility

- Also ideal for tight spaces or hard-to-reach places.
- Wireless freedom of movement and flexible use.
- Can be stored anywhere thanks to its compact design.



Professional quality: particularly robust and durable

- Efficient turbine with a service life of 1000 hours.
- Very robust and hard-wearing diaphragm pump.
- Compact, extra-short and hard-wearing upholstery nozzle.

ACCESSORIES FOR PUZZI 2/1 BP 1.101-750.0



		Order no.	Description	
SPRAY EXTRACTION MACHINES				
Upholstery tools				
Upholstery nozzle short PuZZi	1	2.885-940.0	Ideal in confined areas: very short and ergonomic upholstery nozzle with integrated handle (DN 32) made of plastic for deep cleaning with the PuZZi spray extraction cleaner from Kärcher.	■
Spray/suction hoses				
Spray/suction hose for PuZZi, 2/1 Bp, 1.9 metres long	2	2.885-913.0	Spray/suction hose, 1.9 metres long, for PuZZi 2/1 Bp battery-powered spray extraction cleaners from Kärcher. Only suitable for use with the short, ergonomic Professional PuZZi upholstery nozzle.	■
BATTERIES				
Battery Power 36/25	3	2.445-030.0	36 V / 2.5 Ah Kärcher Battery Power exchangeable battery with innovative Real Time Technology incl. LCD display to indicate battery level. Suitable for use in all devices on the 36 V Kärcher battery platform.	□
Battery Power 36/50	4	2.445-031.0	36 V / 5.0 Ah Battery Power exchangeable battery with innovative Real Time Technology incl. LCD display to show the battery level. Suitable for all devices on the 36 V Kärcher battery platform.	□
BATTERY CHARGERS				
Fast Charger Battery Power 36 V	5	2.445-033.0	With the fast charger, the 36 V/2.5 Ah exchangeable battery can be charged to 80% in just 48 minutes. Also suitable for all other batteries on the 36 V Kärcher battery platform.	□
STARTERKIT BATTERIES AND BATTERY CHARGERS				
Starter kit Battery Power 36/25	6	2.445-064.0	The Battery Power 36/25 Starter Kit includes a 36 V/2.5 Ah Battery Power exchangeable battery and a 36 V fast charger. For all devices on the 36 V Kärcher battery platform.	□
Starter kit Battery Power 36/50	7	2.445-065.0	Battery Power 36/50 Starter Kit incl. 36 V/5.0 Ah Battery Power exchangeable battery and 36 V fast charger. Suitable for use in all devices on the 36 V Kärcher battery platform.	□
BATTERIES				
Battery Power+ 36/75	8	2.445-043.0	A capacity of 7.5 Ah guarantees long runtimes for the Battery Power+ 36 V lithium-ion battery. Very powerful, with Real Time Technology via LCD display and protection against overcurrent.	□
Battery Power+ 36/60	9	2.042-022.0	Extremely powerful Battery Power+ 36 V lithium-ion battery with a capacity of 6.0 Ah for a long runtime. With innovative Real Time Technology via LCD display and voltage monitoring.	□
BATTERY CHARGERS				
Universal charger Battery Power+ 18-36	10	2.445-054.0	Universal charging unit Battery Power+ with LED operating status indicator for charging all 18 and 36 V Kärcher Battery Power and Kärcher Battery Power+ lithium-ion batteries. Suitable for wall mounting.	□
Fast charger Battery Power+ 36/60	11	2.445-045.0	Charge all 36 V Kärcher Battery Power and Kärcher Battery Power+ lithium-ion batteries with max. 6 A charging current: Quick charger with LED operating status indicator. Easy wall mounting.	□
STARTER KIT				
Starter kit Battery Power+ 36/75	12	2.445-070.0	Starter Kit Battery Power+ 36/75 with 2 36-V/7.5-Ah batteries and 36-V quick charger for our 36 V Kärcher Battery Power and Kärcher Battery Power+ battery platform devices.	□
Starter kit Battery Power+ 36/60	13	2.445-071.0	Kärcher Battery Power+ 36/60 Starter Kit for all machines in the Kärcher 36 V Battery Power+ battery platform. Scope of delivery: 2x 36 V/6.0 Ah batteries and the compatible 36 V quick charger.	□

■ Included in the scope of supply. □ Available accessories.