



Cut



Medium Duty

Medium-duty safety gloves with a firm grip, ensuring greater cut and abrasion protection

- **Varied capabilities:** Besides providing excellent cut and abrasion protection and a firm grip, especially in dry and slightly oily environments, EDGE[®] 48-702 microfoam nitrile gloves also ensure higher tactile sensitivity and dexterity compared to foam nitrile gloves
- **Safety compliance:** Combining quality and affordability, these cost-effective protective gloves boast EN 420 (general requirements) and EN 388 (mechanical hazards) safety standard compliance
- **Optimized comfort:** Featuring a seamless liner and a coated palm that is thinner than most comparable NBR gloves, EDGE[®] 48-702 industrial gloves' breathable coating keeps hands cool and dry
- **Food handling compliance:** Composed of FDA-compliant materials, these safety gloves are suitable for handling and packaging food



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Oil and gas

Applications

- Handling slightly oily metal parts and sheets
- Assembling metal parts and components
- General maintenance

Key Features

- **Microfoam nitrile coating:** For work gloves with grip and dexterity
- **Mechanical risk protection:** Conforms to EN 420 and EN 388 standards
- **Seamless design:** Comfortable, breathable and flexible work gloves

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



4X42B

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-702	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: HPPE, Nylon, Polyester, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	220 to 270 mm, 8.66-10.63 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699