



Cut protection

# KRYTECH 815

High risk - ISO D



CUT PROTECTION  
**LEVEL D**

EN388



4X43D

CATEGORY 2



ISO 13997:

20 N

DEXTERITY

EN ISO 21420:  
5/5



High cut protection without any compromise on comfort and dexterity. Usable with touch screens.

## SPECIFIC ADVANTAGES



### Cut protection

- High cut protection without any compromise on comfort, dexterity and breathability. Usable with touch screens.



### Comfort

- A seamless plaited glove for very good fit, dexterity and flexibility.



### Durability

- Crotch reinforcement for enhanced durability. It offers better productivity and optimizes your costs.



### Suitable for touchscreen

- Can be used with touch devices & touch screen (thumb & index)



### Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



### Washability

- Washable up to 3 times at 60°C , allowing to extend glove lifespan, reduce costs and waste.



### Practical

- Cut level easy to identify thanks to the marking on the back of the glove.

## INDUSTRIES

- Automotive/mechanical industry
- Construction Industry (Carpenters/Joiners)
- Construction Industry (Metalworkers/Locksmiths)
- Glass industry
- Industrial equipment / Metal transformation
- Industrial maintenance

## APPLICATIONS

- Handling and installing metal structures
- Installing steel structures
- Handling glass sheets
- Mechanical maintenance
- Maintenance with cut risk
- Handling of thick metal sheets
- Assembly of thin metal sheets
- Cutting aluminium strips
- Handling sheet metal
- Metal working



Cut protection

# KRYTECH 815

High risk - ISO D


## LEGENDS

EN388

MECHANICAL HAZARDS



PERFORMANCE LEVELS (X = NOT TESTED)



## PRODUCT DETAILS

Interior finish	Seamless textile support from HDPE fibres
Gauge	13
Exterior finish	Ventilated back
Material	Polyurethane
Cuff characteristic	Knitted Cuff
Colour.s	Black Grey
European sizes	6 7 8 9 10 11

## LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 48 pairs/carton
-----------	---

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: on going
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE