


Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KBKO06MPX

COUPLING HALF: Coupler

CONNECTION TYPE: Tube

FUNCTION: Double Shut-Off

CONNECTION SIZE: 4x6 MM

BODY MATERIAL: Brass

PRODUCT OVERVIEW

Parker's Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:

- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

INDUSTRY	General Industrial
INDUSTRY	Healthcare & Life Sciences
WEIGHT	0.011 kg
INTERCHANGE TYPE	European Profile
BRAND	Rectus
MAXIMUM OPERATING PRESSURE	35 bar
APPLICATION	Industrial Machinery
VALVE INCLUDED	Yes
QUANTITY PER BOX	10.0
MAXIMUM OPERATING TEMPERATURE	100 °C
APPLICATION	Medical
DIVISION	Low Pressure Connectors Europe Division
PRODUCT STYLE	Quick Connect
BODY MATERIAL	Brass
VALVE TYPE	Standard Valve
PRODUCT TYPE	Pneumatic Quick Couplings
MAXIMUM OPERATING TEMPERATURE	212 °F
FLOW RATE	130 L/min (air)
OPERATION TYPE	Sleeve
SLEEVE MATERIAL	Brass
HEX SIZE	9 mm (external)

MINIMUM OPERATING TEMPERATURE	-20 °C
TECHNOLOGY	Pneumatics
REGION OF ORIGIN	Germany
PLATING TYPE	Without Surface Treatment
APPLICATION	Pharma
CONNECTION SIZE	4x6 mm
LENGTH	34 mm
COUPLING HALF	Coupler
CONNECTION TYPE	Tube With hose nut, without spring guard
APPLICATION	Food & Beverages
MAXIMUM OPERATING PRESSURE	507 psi
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
SEAL MATERIAL	NBR
FUNCTION	Double Shut-Off
COMPATIBLE FITTING	Series 20 Plug
MINIMUM OPERATING TEMPERATURE	-4 °F
DIAMETER	2.7 mm (nominal)
DIVISION	Low Pressure Connectors Europe Division
PRODUCT SERIES	Series 20
BRAND	Parker