

# AlphaTec™

## 87-195

Extra lightweight natural rubber glove with flocked lining

Previously known as: VersaTouch® 87-195

## Ultralight, highly tactile food processing gloves, specially treated to reduce allergy risks

- **Food handling compliance:** AlphaTec® 87-195 safety gloves possess EU and FDA food handling certification
- **Reduced allergens:** They are also specially treated to reduce the risk of allergic reactions
- **Elevated comfort:** AlphaTec® 87-195 industrial gloves benefit from 100% cotton-flocked lining, lessening perspiration and discomfort
- **Specialized protection:** They also boast EN 374 Type B chemical defenses, protecting against mild acids, animal fats, oil, detergents and alcohols
- **Heightened tactility:** Their super-thin composition means they boast high levels of tactile sensitivity, for more precise handling
- **Augmented dexterity:** An ultra-lightweight design also makes these AlphaTec® gloves dexterous and maneuverable

### Industries

- Janitorial / Sanitation
- Food Processing
- Agriculture
- Chemical

### Applications

- Cleaning
- All food processing applications that have food contact
- Fruit and Vegetable Processing
- Laboratory maintenance and clean up
- Janitorial use



# AlphaTec™

## 87-195

Extra lightweight natural rubber glove with flocked lining

Previously known as: VersaTouch® 87-195

### Key Features

- **Food handling certification:** For EU- and FDA-certified PPE gloves
- **Treated natural rubber:** Reduced risk of allergic reactions
- **Cotton flocking:** Moisture absorbency, for comfortable hand protection

### Vulcanization Chemical Accelerators

- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.



### Performance Standards



0493

EN388: 2016



1000X

EN388: 2016



1010X

EN 421



EN 421



EN ISO 374-1:2016

Type B



KLT

EN ISO 374-1:2016

Type B



KLT

EN ISO 374-1:2016

Type B



KLT

EN ISO 374-5



VIRUS

EN ISO 374-5



VIRUS

EN ISO 374-5



VIRUS

EN 421



### Specifications

BRAND   STYLE	DESCRIPTION	SIZE	Length (MM/INCHES)	COLOR	PACKAGE
AlphaTec® 87-195	<b>Liner Material:</b> Cotton Flocking <b>Coating Material:</b> Natural Rubber Latex	7, 8, 9, 10, 11	305 / 12	Blue	<ul style="list-style-type: none"> <li>• 12 pairs per bag, 12 bags per carton</li> </ul>

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

