


## Features

- All RS PRO soldering tips feature an individual galvanized ferrous coating
- The solder area of the tip also comes tin-plated
- Constructed with a copper core

## RS PRO Soldering Iron Tips Series



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Soldering Iron Tips Series

RS PRO offers a comprehensive range of soldering tips to complement their soldering irons and desoldering irons. Soldering iron tips are available in a variety of sizes, diameters and shapes. Every soldering tip is designed for a specific application.

#### Features and Benefits:

- Constructed with a copper core, the tips provide the most effective level of heat transfer to the solder point.
- High Thermal Conductivity- Ensures fast and efficient heat transfer.
- Durable and Long-Lasting- Made from high-quality materials to extend lifespan.
- Fast Heating and Recovery -improves work efficiency and precision.
- Easy to Replace and Install-Hassle-free maintenance and convenience.
- Multiple Tip Shapes Available-Suitable for different soldering applications.

## General Specifications

|             |             |
|-------------|-------------|
| Tip Shape   | See details |
| For Use Wit | See details |
| Tip Size    | See details |
| Tip Angle   | See details |
| Tip Series  | See details |

| Image                                                                               | Stock No. | Tip Shape | For Use With | Tip Size | Tip Angle | Tip Series |
|-------------------------------------------------------------------------------------|-----------|-----------|--------------|----------|-----------|------------|
|  | 0631080   | Chisel    | 0631068      | 2.4mm    | 0°        | T60        |

|                                                                                     |                  |                  |                     |                 |                  |                   |
|-------------------------------------------------------------------------------------|------------------|------------------|---------------------|-----------------|------------------|-------------------|
|    | 0631081          | Round            | 0631068             | 1mm             | 0°               | T60               |
|    | 0631082          | Conical          | 0631068             | 0.5mm           | 0°               | T60               |
|    | 0631083          | Chisel           | 0631068             | 1.2mm           | 0°               | T60               |
|    | 0631084          | Round            | 0631068             | 1mm             | 0°               | T60               |
|    | 0631085          | Chisel           | 0631068             | 4mm             | 0°               | T60               |
|                                                                                     | <b>Stock No.</b> | <b>Tip Shape</b> | <b>For Use With</b> | <b>Tip Size</b> | <b>Tip Angle</b> | <b>Tip Series</b> |
|    | 0631087          | Conical          | 0631071             | 0.4mm           | 0°               | T80               |
|    | 0631088          | Round            | 0631071             | 0.4mm           | 0°               | T80               |
|    | 0631089          | Chisel           | 0631071             | 1.2mm           | 0°               | T80               |
|    | 0631090          | Chisel           | 0631071             | 0.8mm           | 0°               | T80               |
|  | 0631091          | Chisel           | 0631071             | 1.6mm           | 0°               | T80               |
|  | 0631093          | Conical          | 0631071             | 0.3mm           | 0°               | T80               |
|  | 0631094          | Chisel           | 0631071             | 2.4mm           | 0°               | T80               |
|  | 0631095          | Conical          | 0631071             | 0.4mm           | 30°              | T80               |
|  | 0631096          | Chisel           | 0631071             | 4.5mm           | 0°               | T80               |
|  | 0631097          | Chisel           | 0631066             | 2.4mm           | 0°               | T690              |
|  | 0631098          | Round            | 0631066             | 1mm             | 0°               | T690              |
|  | 0631099          | Round            | 0631066             | 0.5mm           | 0°               | T690              |
|  | 0631100          | Chisel           | 0631066             | 1.2mm           | 0°               | T690              |
|  |                  | Chisel           |                     | 1.6mm           | 0°               | T690              |

# Soldering Iron Tips



|                                                                                   |         |        |         |       |    |      |
|-----------------------------------------------------------------------------------|---------|--------|---------|-------|----|------|
|                                                                                   | 0631101 |        | 0631066 |       |    |      |
|  | 0631102 | Chisel | 0631066 | 3.2mm | 0° | T690 |

## Approvals

|              |           |
|--------------|-----------|
| Declarations | REACH DoC |
|--------------|-----------|

## Similar Products

| Stock No. | Brand  | Product Name   | Tip Shape | Tip Size | Tip Angle | For Use With                 |
|-----------|--------|----------------|-----------|----------|-----------|------------------------------|
| 0631080   | RS PRO | Soldering Tips | Chisel    | 2.4mm    | 0°        | Soldering Station<br>0631068 |
| 0631081   | RS PRO | Soldering Tips | Round     | 1mm      | 0°        | Soldering Station<br>0631068 |
| 0631082   | RS PRO | Soldering Tips | Conical   | 0.5mm    | 0°        | Soldering Station<br>0631068 |
| 0631083   | RS PRO | Soldering Tips | Chisel    | 1.2mm    | 0°        | Soldering Station<br>0631068 |
| 0631084   | RS PRO | Soldering Tips | Round     | 1mm      | 0°        | Soldering Station<br>0631068 |
| 0631085   | RS PRO | Soldering Tips | Chisel    | 4mm      | 0°        | Soldering Station<br>0631068 |
| 0631087   | RS PRO | Soldering Tips | Conical   | 0.4mm    | 0°        | Soldering Station<br>0631071 |
|           | RS PRO | Soldering Tips | Round     | 0.4mm    | 0°        | Soldering Station            |

# Soldering Iron Tips



|         |        |                |         |       |     |                                       |
|---------|--------|----------------|---------|-------|-----|---------------------------------------|
| 0631088 |        |                |         |       |     | 0631071                               |
| 0631089 | RS PRO | Soldering Tips | Chisel  | 1.2mm | 0°  | Soldering Station<br>0631071          |
| 0631090 | RS PRO | Soldering Tips | Chisel  | 0.8mm | 0°  | Soldering Station<br>0631071          |
| 0631091 | RS PRO | Soldering Tips | Chisel  | 1.6mm | 0°  | Soldering Station<br>0631071          |
| 0631093 | RS PRO | Soldering Tips | Conical | 0.3mm | 0°  | Soldering Station<br>0631071          |
| 0631094 | RS PRO | Soldering Tips | Chisel  | 2.4mm | 0°  | Soldering Station<br>0631071          |
| 0631095 | RS PRO | Soldering Tips | Conical | 0.4mm | 30° | Soldering Station<br>0631071          |
| 0631096 | RS PRO | Soldering Tips | Chisel  | 4.5mm | 0°  | Soldering Station<br>0631071          |
| 0631097 | RS PRO | Soldering Tips | Chisel  | 2.4mm | 0°  | Soldering Station XXX-<br>XXX 0631066 |
| 0631098 | RS PRO | Soldering Tips | Round   | 1mm   | 0°  | Soldering Station XXX-<br>XXX 0631066 |
| 0631099 | RS PRO | Soldering Tips | Round   | 0.5mm | 0°  | Soldering Station XXX-<br>XXX 0631066 |
| 0631100 | RS PRO | Soldering Tips | Chisel  | 1.2mm | 0°  | Soldering Station XXX-<br>XXX 0631066 |
| 0631101 | RS PRO | Soldering Tips | Chisel  | 1.6mm | 0°  | Soldering Station XXX-<br>XXX 0631066 |
| 0631102 | RS PRO | Soldering Tips | Chisel  | 3.2mm | 0°  | Soldering Station XXX-<br>XXX 0631066 |

## Soldering Station

| Stock No. | Brand  | Product Name      | Wattage | Tasks Support           | Plug Type       |
|-----------|--------|-------------------|---------|-------------------------|-----------------|
| 0631067   | RS PRO | Soldering Station | 60W     | Desoldering / Soldering | Type G & Type E |
|           | RS PRO | Soldering Station | 80W     | Desoldering / Soldering | Type G & Type E |



# Soldering Iron Tips















|         |           |                   |     |                         |                    |
|---------|-----------|-------------------|-----|-------------------------|--------------------|
| 0631068 |           |                   |     |                         |                    |
| 0631069 | RS<br>PRO | Soldering Station | 70W | Desoldering / Soldering | Type G &<br>Type E |
| 0631071 | RS<br>PRO | Soldering Station | 80W | Desoldering / Soldering | Type G &<br>Type E |
| 0631072 | RS<br>PRO | Soldering Station | 60W | Desoldering / Soldering | Type G &<br>Type E |
| 0631066 | RS<br>PRO | Soldering Iron    | 90W | Desoldering / Soldering | Type G &<br>Type E |

## Soldering Iron

| Stock No. | Brand     | Product Name   | Wattage | Temperature Range | For Use With                         |
|-----------|-----------|----------------|---------|-------------------|--------------------------------------|
| 0631076   | RS<br>PRO | Soldering Iron | 60W     | 200-480 °C        | Soldering Station<br>0631072 xxx-xxx |
| 0631077   | RS<br>PRO | Soldering Iron | 60W     | 100-500 °C        | Soldering Station<br>0631067 xxx-xxx |
| 0631078   | RS<br>PRO | Soldering Iron | 80W     | 150-550 °C        | Soldering Station<br>0631071 xxx-xxx |
| 0631079   | RS<br>PRO | Soldering Iron | 70W     | 50-500 °C         | Soldering Station<br>0631069 xxx-xxx |



|                                                                                    |                                                                                    |                                                                                     |
|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|   |   |    |
| XXX-XXXX                                                                           | XXX-XXXX                                                                           | XXX-XXXX                                                                            |
| T690-2.4D                                                                          | T690-B                                                                             | T690-I                                                                              |
|  |  |  |
| XXX-XXXX                                                                           | XXX-XXXX                                                                           | XXX-XXXX                                                                            |
| T690-1.2D                                                                          | T690-1.6D                                                                          | T690-3.2D                                                                           |

|                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  |  |  |    |  |
| XXX-XXXX                                                                            | XXX-XXXX                                                                            | XXX-XXXX                                                                            | XXX-XXXX                                                                              | XXX-XXXX                                                                              |
| T80-D08                                                                             | T80-I                                                                               | T80-B                                                                               | T80-D16                                                                               | T80-ILS                                                                               |
|  |  |  |  |                                                                                       |
| XXX-XXXX                                                                            | XXX-XXXX                                                                            | XXX-XXXX                                                                            | XXX-XXXX                                                                              |                                                                                       |