

1041-002

PROFI-tool assortment in case

100 pieces

Code	ETIM
3082148	EC000149
EAN	UNSPSC
4010886950869	27-11-32-01
Country of origin	eCl@ss
China	21-04-90-90
Customs tariff number	
82060000	



Article description

- Professional set for all trades
- A practical assortment for on-site use
- Packed in a strong plastic case made from impact-proof ABS
- Robust aluminium frame
- Robust companion - whenever the right tools have always to be at hand

Article parts list

Combination spanner No. 1 B, 8 10 13 17 19 22 mm ,1/2" Socket No. 19, 8 10 13 17 19 22 mm ,1/2" Extension No. 1990-5, 1/2" Reversible ratchet No. 1993 U-20 ,Spring Socket rail for 14 inserts 1/2" VH 19 ,1/4" Bit socket box No. 666-U-20, with ratchet 35 pcs ,Allen Key set No. H 42-10, in holder 10 pcs ,Offset screwdriver set TX No. H 43 TX-88 in holder 8 pcs ,Adjustable open-end wrench No. 60 P 8, 8" ,Percussion tool set No. 106, 6 pcs. ,Grip pliers No.137 10, 10" ,Square awl No. 156 S ,Non-return soft-face and engineer's hammer KOMBI-PLUS R No. 247 H-30 ,Hobby saw No. 406 ,Cable knife No. 0513-09 ,Spark plug brush No. 647 ,Pocket caliper No. 710 ,3C-Screwdriver slotted No. 2150, 3 4 5.5 6.5 8 mm ,3C-Screwdriver philips No. 2160, PH 0 1 2 ,3C-Screwdriver pozi No. 2160, PZ 1 2 ,Steel tape measure No. 4534-3, tape L. 3 m ,Voltage detector slotted No. 4615 3, 220-250 V, 3mm ,Small universal scissors No. 8096-140 ,Wire stripper No. 8098-160 JC, 160 mm 2C-handle ,Multiple pliers No. 8133-200 JC, 200 mm 2C-handle ,Combination pliers 8245-180 JC, 180 mm 2C-handle ,Power side cutter No. 8316-160 JC, 160 mm 2C-handle ,Universal pliers No. 142 10 TL, 10" ,+ Tool case No. WK 1041 L

Article information

Contents (Qty of pieces)	100	Total height [mm]	185 mm
reversible arms available	no	Total depth [mm]	395 mm
Net weight [kg]	12,9 kg	Material	Acrylnitril-Butadien-Styrol (ABS)
Total width [mm]	490 mm	Storage	Case