

ARC 4 SWITCHING DUNGAREE WITH PYRAD® TECHNOLOGY BY GORE-TEX LABS

9515M & 9515F

PRODUCT DESCRIPTION

This revolutionary dungaree delivers 40 cal/cm² Arc Flash protection in a lightweight, single-layer design. Unlike traditional bulky arc protection garments, the ProGARM® Arc 4 Switching Dungaree is crafted to enhance freedom of movement without compromising safety. The soft-for-bending material allows wearers to perform their tasks with greater agility, minimising muscular fatigue even during physically demanding activities.

PRODUCT DETAILS

FITS: Male & Female
LENGTHS: Short | Regular | Tall
MALE SIZES: S-5XL (9515M)
FEMALE SIZES: 6-24 (9515F)
COLOUR: Grey

MATCHING PRODUCTS

JACKET:
9505M & 9505F

HOOD:
9501 - One size

BOX TEST ARC RATING



EN STANDARDS

EN ISO 11612: 2015	EN 1149-5: 2018	EN 61482-2: 2020
A1, B2, C1, F1	Pt. 5:2018 Pt. 3:2004 Charge Decay	APC 2 ELIM = 40cal



ARC 4 SWITCHING DUNGAREE WITH PYRAD® TECHNOLOGY BY GORE-TEX LABS

9515M & 9515F

FEATURES & BENEFITS

- ✓ Easily adjustable braces using 260°C heat resistant buckles
- ✓ Studs side opening for easier donning and doffing
- ✓ Adjustable waist band using 260°C heat resistant buckles
- ✓ Shaped knee panelling
- ✓ Leg opening with FR spiral zip, adjustable leg hem
- ✓ SafetyICON with ELIM rating
- ✓ FR HEX Heat applied reflective tape for added visibility
- ✓ Lightweight PYRAD® Technology by GORE-TEX Labs

PRODUCT INFORMATION

FABRIC SPECIFICATION:


Weight: 320gms
Pyrad® Technology
by GORE-TEX Labs



Lightweight PYRAD® Technology by GORE-TEX Labs

PRODUCT CARE:

- ✓ Washing Temperature: 60°C
- ✓ Drying Temperature: up to 60°C
- ✓ Do not iron
- ✓ Do not dry clean
- ✓ Do not use bleach



More comfortable during high-intensity activities



ARC RATED PROTECTION



BREATHABLE



LIGHTWEIGHT



COMFORT FIT



LIFETIME SEAM
GUARANTEE



Increased ease of motion with less muscular fatigue

ARC 4 SWITCHING DUNGAREE

WEARER FIT GUIDE - MALE

BODY MEASUREMENTS

SIZE	WAIST (cm / Inches)	SEAT (cm / Inches)
Small	76-84cm / 30-33"	86-94cm / 34-37"
Medium	84-92cm / 33-36"	94-102cm / 37-40"
Large	92-100cm / 36-39"	102-110cm / 40-43"
X-Large	100-108cm / 39-42"	110-118cm / 43-46"
2X-Large	108-116cm / 42-45"	118-126cm / 46-50"
3X-Large	116-124cm / 45-49"	126-134cm / 49-53"
4X- Large	124-132cm / 49-52"	134-142cm / 53-56"
5X-Large	132-138cm / 52-54"	142-150cm / 56-58"

GARMENT LENGTH

SIZE	WEARER HEIGHT (cm / Inches)	WEARER INSIDE LEG (cm / Inches)
Short	157-170cm 5'2"-5'7"	74cm 29"
Regular	170-180cm 5'7"-5'11"	79cm 31"
Tall	180-188cm 5'11"-6'2"	84cm 33"

MEASURING GUIDE

Measurements must be taken wearing clothing usually worn underneath waterproof outerwear. The tape measure should be fairly loose and not pulled too tight.

- ✓ **CHEST** - measure under the arms at the fullest part around the chest horizontally with arms by your side
- ✓ **WAIST** - measure around the natural waistline at the fullest part
- ✓ **SEAT** - with the feet together measure around the fullest part of the hips
- ✓ **HEIGHT** - with bare feet together measure from the top of the head to the floor
- ✓ **INSIDE LEG** - in bare feet take the measurement from the top of the inside leg and measure down the inside leg to the floor


Once measurements are taken compare them to the fit guide measurement tables to find your Jacket and Trouser size.

When fitting the Trouser if the waist and seat measurements fall into different size categories then choose the larger size to ensure the trouser is not too close fitting.

If the height and inside leg measurements fall into different length categories then choose the jacket length based on the height measurement and the trouser length based on the inside leg measurement.

**These styles are historically perceived as MALE but can be worn by any person who's body measurements fit into the above tables.*

***Please note when using the measurement tables that all manufacturing tolerances and standard garment over-measures have been taken into account. This ensures any slight variances in manufacture or fabric shrinkage after washing will not affect the fit of the garments.*



ARC 4 SWITCHING DUNGAREE

WEARER FIT GUIDE - FEMALE

BODY MEASUREMENTS

SIZE	BUST (cm / Inches)		WAIST (cm / Inches)		HIP (cm / Inches)	
2	82-90cm	32-35"	68-76cm	27-30"	86-94cm	34-37"
8	90-98cm	35-38"	76-84cm	30-33"	94-102cm	37-40"
10	98-106cm	38-42"	84-92cm	33-36"	102-110cm	40-43"
12	106-114cm	42-45"	92-100cm	36-39"	110-118cm	43-46"
14	114-122cm	45-48"	100-108cm	39-42"	118-126cm	46-50"
16	122-130cm	48-51"	108-116cm	42-45"	126-134cm	50-53"
18	130-138cm	51-54"	116-124cm	45-49"	134-142cm	53-56"
20	138-146cm	54-58"	124-132cm	49-52"	142-150cm	56-59"
22	146-154cm	58-61"	132-140cm	52-55"	150-158cm	59-62"
24	154-162cm	61-64"	140-148cm	55-58"	158-166cm	62-65"

GARMENT LENGTH

SIZE	WEARER HEIGHT (cm / Inches)	WEARER INSIDE LEG (cm / Inches)
Short	157-170cm 5'2"-5'7"	74cm 29"
Regular	170-180cm 5'7"-5'11"	79cm 31"
Tall	180-188cm 5'11"-6'2"	84cm 33"

MEASURING GUIDE

Measurements must be taken wearing clothing usually worn underneath waterproof outerwear. The tape measure should be fairly loose and not pulled too tight.

- ✓ **BUST** - measure under the arms at the fullest part around the bust horizontally with arms by your side
- ✓ **WAIST** - measure around the natural waistline at the fullest part
- ✓ **HIP** - with the feet together measure around the fullest part of the hips
- ✓ **HEIGHT** - with bare feet together measure from the top of the head to the floor
- ✓ **INSIDE LEG** - in bare feet take the measurement from the top of the inside leg and measure down the inside leg to the floor

Once measurements are taken compare them to the fit guide measurement tables to find your Jacket and Trouser size.

When fitting the Trouser if the waist and seat measurements fall into different size categories then choose the larger size to ensure the trouser is not too close fitting.

If the height and inside leg measurements fall into different length categories then choose the jacket length based on the height measurement and the trouser length based on the inside leg measurement.

**These styles are historically perceived as FEMALE but can be worn by any person who's body measurements fit into the above tables.*

***Please note when using the measurement tables that all manufacturing tolerances and standard garment over-measures have been taken into account. This ensures any slight variances in manufacture or fabric shrinkage after washing will not affect the fit of the garments.*

