








LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE	APPD
AD	39												REV PER 063C-0203-04	14OCT04	JR/DS

- 1 OBSOLETE PART NO.
- 2 "AMP", PART NO. AND DATE CODE MARKED (WHITE), .062±.015 CHARS. WHEN HOUSING SIZE PERMITS
- 3 .046±.015 CHARS. MARKED (WHITE) FIRST AND EVERY 5TH CAVITY, ONE SIDE.
- 4 SUPERSEDED BY 5-87456-5.
- 5 SUPERSEDED BY 3-87456-3.
- 6 SUPERSEDED BY 4-87456-5.



PART NO.	NO. OF POSITIONS	C	A	PART NO. MARKED	
6-87456-5	81.28 [3.200]	31	64	6-87456-6	
6-87456-3	73.66 [2.900]	28	58	6-87456-4	
6-87456-1	71.12 [2.800]	27	56	6-87456-2	
5-87456-9	60.96 [2.400]	23	48	6-87456-0	
5-87456-7	83.82 [3.300]	32	66	5-87456-4	
5-87456-5	88.90 [3.505]	34	70	5-87456-6	
5-87456-3	2.67 [0.105]	-	2	-	
5-87456-1	76.33 [3.005]	29	60	5-87456-2	
4-87456-9	5.21 [0.205]	1	4	5-87456-0	
4-87456-7	91.57 [3.605]	35	72	4-87456-8	
4-87456-5	68.71 [2.705]	26	54	4-87456-6	
4-87456-3	53.47 [2.105]	20	42	4-87456-4	
4-87456-1	66.17 [2.605]	25	52	4-87456-2	
3-87456-9	63.63 [2.505]	24	50	4-87456-0	
3-87456-7	56.01 [2.205]	21	44	3-87456-8	
3-87456-5	50.93 [2.005]	19	40	3-87456-6	
3-87456-3	48.39 [1.905]	18	38	3-87456-4	
3-87456-1	45.85 [1.805]	17	36	3-87456-2	
2-87456-9	43.31 [1.705]	16	34	3-87456-0	
2-87456-7	40.77 [1.605]	15	32	2-87456-8	
2-87456-5	38.23 [1.505]	14	30	2-87456-6	
2-87456-3	35.69 [1.405]	13	28	2-87456-4	
2-87456-1	33.15 [1.305]	12	26	2-87456-2	
1-87456-9	30.61 [1.205]	11	24	2-87456-0	
1-87456-7	28.07 [1.105]	10	22	1-87456-8	
1-87456-5	25.53 [1.005]	9	20	1-87456-6	
1-87456-3	22.99 [0.905]	8	18	1-87456-4	
1-87456-1	20.45 [0.805]	7	16	1-87456-2	
87456-9	17.91 [0.705]	6	14	1-87456-0	
87456-7	15.37 [0.605]	5	12	87456-8	
87456-5	12.83 [0.505]	4	10	87456-6	
87456-3	10.29 [0.405]	3	8	87456-4	
87456-1	7.75 [0.305]	2	6	87456-2	
PART NO. WITHOUT MARKING		C	A	NO. OF POSITIONS	PART NO. MARKED

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± .02 3 PLC DEC ± .005 ANGLES ± 0°30'		DR 11-06-92 E. BRANDBERG		<b>AMP</b> AMP Incorporated Harrisburg, PA 17105-3608	
CHK 11-30-92 J. GESFORD		APPD 11-30-92 J. GESFORD			
MATERIAL: GLASS FILLED NYLON COLOR BLACK PER ASTM D4066		APPD 12-1-92 D. DUPLER		NAME: HOUSING, MOD IV DOUBLE ROW, .100X.100 CL CRIMP SNAP-IN, SHORT ENTRY	
FINISH: -		APPLICATION SPEC: -		SIZE: D	CAGE CODE: 00779
WEIGHT: -		DRAWING NO: C-87456		SCALE: 4:1	SHEET: 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.