

Koolbreeze

Wholesale Climate Control Solutions

Climate King

1-Phase 240V and 3-Phase 400V

Premium Torpedo Electric Fan Heaters

(2019 Models)



HCK-TP15 (2019 Model) HCK-TP30 (2019 Model)



HCK-TP9



HCK-TP5



HCK-TP3UK

The Climate King TP series is a range of heavy duty industrially styled electric cylinder fan heaters. Available as either 1-Phase 240V and 400V 3-Phase, models the TP series encompasses heat outputs from 3kW up to 30kW. Each model in the range has a stainless steel heating element, metal fan blades, selectable heat output levels and adjustable thermostats for high efficiency. The model range also features quality powder coated steel cases, with the smaller models having a support frame with integrated carrying handle and the larger models having an integrated wheeled trolley making them ideal for use in workshops, garages, greenhouses and building sites. The smaller 1-Phase 240V and 3-Phase 400V models are supplied with either an integrated power cord fitted with a UK plug or a 3-Phase cable and connector. The larger 3-Phase 400V models are equipped with a 3-Phase 5 pin socket on the unit and require a separate 3-Phase power cable of the correct rating and type (not supplied).

For information on the power cord requirements for the larger 400V 3-Phase models please see the specification table below.

Model Range Specifications*

Model	RS Product Code	Description	Electrical Supply	Power Cord Specifications	Heat Output	Dimensions	Weight
HCK-TP3UK	124-5248	3kW Torpedo Fan Heater	1-Phase 240V 13A 50Hz	13 amp UK Plug (FITTED)	1.5kW/3kW	315 x 330 x 400 mm	6.6kg
HCK-TP5	124-5249	5kW Torpedo Fan Heater	3-Phase 400V 16A 50Hz	16A 3-Phase 5 pin connector and cable (SUPPLIED)	2.5kW/5kW	315 x 330 x 400 mm	7.6kg
HCK-TP9	124-5250	9 kW Torpedo Fan Heater	3-Phase 400V 16A 50Hz	16A 3-Phase 5 pin connector and cable (SUPPLIED)	4.5kW/9kW	335 x 335 x 415 mm	11.4kg
HCK-TP15	144-4360	15kW Torpedo Fan Heater	3-Phase 400V 32A 50Hz	32A 3-Phase 5 pin lead and cable (NOT SUPPLIED)	5kW/10kW/15kW	495 X 520 X 860 mm	21.7kg
HCK-TP30	144-4361	30kW Torpedo Fan Heater	3-Phase 400V 63A 50Hz	63A 3-Phase 5 pin lead and cable (NOT SUPPLIED)	15kW/30kW	645 X 565 X 860 mm	31.2kg

*Due to constant product innovation Koolbreeze reserves the right to make changes to product specifications