



PRODUCT-DETAILS

BER38-4KF

BER38-4KF Connection Set for Reversing Contactors



General Information

| | |
|-----------------------|--|
| Extended Product Type | BER38-4KF |
| Product ID | 1SBN082322R1000 |
| EAN | 3471523131439 |
| Catalog Description | BER38-4KF Connection Set for Reversing Contactors |
| Long Description | <p>BER38-4KF is a connection set used to connect the main poles of two 3-pole AF09..K ... AF38..K, AFC09..K ... AFC38..K contactors mounted side by side.</p> <p>The connection sets are made up of:</p> <ul style="list-style-type: none"> • 1 upstream and 1 downstream connections • Insulated, solid copper bars • Black fork pieces for a quick dismounting of reversing contactors. <p>With the Push-in Spring terminals, one push is all you need for a faster than ever installation, an easier than ever wiring and a reliable as ever connection.</p> |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85389099 |

Popular Downloads

| | |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1SBC100214C0202 |
| Instructions and Manuals | 1SBC101056M6801 |
| Instructions and Manuals (Part 2) | 1SAC200017M0002 |
| CAD Dimensional Drawing | 2CDC001079B0201 |

Dimensions

| | |
|----------------------------|---------|
| Product Net Width | 79 mm |
| Product Net Depth / Length | 30 mm |
| Product Net Height | 39 mm |
| Product Net Weight | 0.08 kg |

Technical

| | |
|---------------------------|---|
| Standards | EN 60947-1, EN 60947-4-1, UL 60947-4-1, CSA C22.2 No. 60947-4-1 |
| Rated Operational Voltage | Main Circuit 690 V AC |
| Rated Frequency (f) | Main Circuit 50 / 60 Hz |
| Terminal Type | Push-in Spring Terminals |
| Suitable For | AF26 AF26Z AF30 AF30Z AF38 AF38Z |
| Product Name | Connection Set |

Material Compliance

| | |
|---|--|
| Conflict Minerals Reporting Template (CMRT) | 9AKK108467A5658 |
| REACH Declaration | 2CMT2021-006202 |
| RoHS Declaration | 2CMT2021-006277 |
| RoHS Information | Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019 |
| WEEE B2C / B2B | Business To Business |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

Certificates and Declarations

| | |
|----------------------------------|--|
| Declaration of Conformity - CE | 1SBD250021U1000 |
| Declaration of Conformity - UKCA | 1SBD250043U1000 |
| GOST Certificate | GOST_POCCFR.ME77.B07175.pdf |
| UL Certificate | UL-US-L312527-151-12119002-5 UL-CA-L312527-451-12119002-5 |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | box 1 piece |
| Package Level 1 Width | 44 mm |
| Package Level 1 Depth / Length | 83 mm |
| Package Level 1 Height | 43 mm |
| Package Level 1 Gross Weight | 0.095 kg |
| Package Level 1 EAN | 3471523131439 |

External Classifications and Standards

| | |
|--------------------|--|
| ETIM 7 | EC002498 - Accessories for low-voltage switch technology |
| ETIM 8 | EC002498 - Accessories/spare parts for low-voltage switch technology |
| ETIM 9 | EC002498 - Accessories/spare parts for low-voltage switch technology |
| eClass | V11.0 : 27371392 |
| UNSPSC | 39120000 |
| E-Number (Finland) | 3709750 |
| E-Number (Sweden) | 3210700 |

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

