

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Wheeled
- Height Adjustable
- Back Adjustable
- Seat Adjustable

RS PRO ESD Economic chair

RS Stock No.: 0665651



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Economic ESD Chair is a reliable solution for environments where electrostatic control is essential, and practical, cost-effective solutions are valued. With a well-thought-out design and functional features, this chair combines efficiency with comfort, delivering excellent performance for daily use in demanding conditions.

Product Features:

- ✓ **High-resilience foam seat** – adapts to the body shape and offers ergonomic comfort throughout the workday
- ✓ **Adjustable seat height, seat depth, and backrest height** – allows personalized setup for optimal support
- ✓ **Durable five-star chrome-plated base** – ensures stability and long-term durability under intensive use
- ✓ **Wear-resistant dissipative fabric** – supports ESD safety and maintains its appearance over time
- ✓ **Conductive castors** – rubber-coated to protect flooring and ensure safe mobility in ESD-sensitive areas
- ✓ **Easy maintenance** – available in various fabric options that are resistant to dirt and simple to clean

An excellent choice for service centers, production environments, and other workplaces where reliable ESD control is required. Thanks to its ergonomic design, the Economic ESD Chair provides day-long comfort and dependable support.

General Specifications

TOTAL HEIGHT (mm)	720-910
TOTAL WIDTH (mm)	640
WEIGHT (kg)	9,5
MAX LOAD CAPACITY (kg)	120 (up to 200 kg with a special gas lift)
HEIGHT ADJUSTMENT RANGE (mm)	480-610mm
SEAT DIMENSIONS (mm)	460 x 440
BACKREST DIMENSIONS (mm)	220 x 360
ESD	YES
COLOUR	BLACK
MATERIAL	STANDARD
BASE MATERIAL	CHROME-PLATED STEEL
CASTORS	CONDUCTIVE, RUBBER-COATED TO PREVENT SCRATCHING
RESISTANCE GROUNDING (0hm)	10 ⁶ – 10 ⁸

Approvals

Chair compliance with standards	PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007
Fabric compliance with standards	PN-EN 1021-1:2014-12, PN-EN 1021-2:2014-12

Similar Products

Stock No.	Brand	Product Name
0665642	RS PRO	ESD PU Stool chair, seat height adjustment 430-555mm
0665643	RS PRO	ESD PU Stool chair, seat height adjustment 510-695mm
0665644	RS PRO	ESD PU Stool chair, seat height adjustment 560-810mm
0665645	RS PRO	ESD PU Hoker chair, seat height adjustment 430-555mm
0665646	RS PRO	ESD PU Hoker chair, seat height adjustment 515-700mm
0665647	RS PRO	ESD PU Hoker chair, seat height adjustment 560-810mm
0665648	RS PRO	ESD Stool chair, seat height adjustment 455-575mm
0665649	RS PRO	ESD Stool chair, seat height adjustment 535-715mm
0665650	RS PRO	ESD Stool chair, seat height adjustment 585-835mm

Accessories

Stock No.	Brand	Product Name
0665661	RS PRO	ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**)
0665662	RS PRO	ESD metal castor, diameter 50mm
0665664	RS PRO	ESD glides
0665665	RS PRO	ESD footrest
0665666	RS PRO	ESD PU armrests
0665668	RS PRO	ESD armrests, black steel + antistatic PU cover
0665670	RS PRO	ESD armrests with height adjustment, black steel + antistatic PU covers