

Product datasheet

Specifications



APC NetShelter Switched Rack PDU, 1U, 1PH, 3.7kW 230V 16A or 3.3kW 208V 16A, 8 C13 outlets, C20 cord

AP7921B

Overview

Presentation	This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.
Lead time	Usually in Stock

Main

Colour	Black
Product or component type	PDU
PDU type	Switched
Cord length	2.5 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets User manual

Complementary

Input Voltage	200 V 208 V 230 V
Height	4.4 cm
Width	44.5 cm
Output Voltage	208 V 230 V
Depth	10.8 cm
Net weight	2.27 kg
Mounting location	Front Rear
Mounting preference	No preference
Input Plug Type	IEC 60320 C20
Mounting mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[In] rated current	16 A
Permissible voltage	200...240 V
Input current limits	20 A
Load capacity	3680 VA
Network frequency	50/60 Hz
Outlet type and quantity	8 IEC 60320 C13

Environment

Product certifications	cUL listed CE CSA GOST IRAM MIC UL listed VDE VCCI
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.0000000000...15240.0000000000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	34.3 cm
Package 1 Length	47 cm
Package 1 Weight	3.45 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	916
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACH Regulation	REACH Declaration

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	Yes