

Previously known as: MICROGARD® 1800 Ts PLUS - Model 156

Sealed seams provide additional protection in low hazard liquid spray applications..

DESIGN

MICROGARD® 1800 Ts PLUS is a lightweight, breathable material and so is particularly suited to warmer working environments. With Stitched and taped seams Provides a good barrier to low hazard liquid spray and fine particulates.

STITCHED AND TAPED SEAMS

Internal stitching which is overtaped to offer increased strength and an effective barrier to liquids and particulates

SUIT FEATURES

- 3 piece hood
- Elasticated hood, wrists, waist and ankles
- 2-way front zipper with resealable storm flap
- Finger Loops
- Chinstrap

COLOURS

White

SIZES

S-3XL

OTHER MODELS IN THE RANGE

Model 103 - Collar

Model 122 - Attached boots with ankle ties and anti-slip soles

Model 156 - Intergarted socks with boot overflaps



Industries

- Life Sciences
- Automotive
- Metal fabrication
- Food Processing
- Chemical
- Automotive Aftermarket


Applications

- Clean room cleaning and preparing
- Body painting including surface inspection
- Production line support & maintenance
- Cleaning of plant and machines
- Maintenance of plant and machines
- Fibre Glass Resin Applications
- Handling of powders


KEY FEATURES & BENEFITS

- Protects against low hazard liquid spray and fine particulates
- Comfortable to wear featuring moisture vapor permeable fabric ("breathable") to help reduce the risk of heat stress
- Optimized body fit, improving wearer comfort and safety
- Anti-static, tested according to EN 1149-5 and AATCC 76
- Low linting to help reduce the risk of cross contamination in critical areas
- Silicone free, critical in spray painting applications

Material Diagram



Seam Diagram



Performance Standards


TYPE 4-B


TYPE 5-B


TYPE 6-B


0598


EN 1073-2


EN 1149-5

EN ISO 13688:2013


EN 14126

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL
Color	White
Country Of Origin	China
Models Available	111, 122
Packaging Overview	Individually Packed
Product Material	Microporous polyethylene Laminate non-woven
Product Reference	1800 Ts PLUS - Model 156
Standards Overview	CE CATEGORY III (Type 4-B, Type 5-B, Type 6-B, EN 1073-2, EN 14126, EN 1149-5)
Seam Type	Stitched and Taped
Shelf Life	5 years

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall, 3-piece hood, single zipper with re-sealable storm flap, finger loops and chin strap. Tunnelled elasticated wrists and hood. Attached boot ends with elasticated leg over flaps.

For additional in formation visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

