

**D 19 L-015**

**SOCKET SET 1/2" 15 pieces**

- With forged, tempered UD profile sockets, hand-operated
- In GEDORIT blue sheet steel case
- Dimensions: 320 x 210 x 55 mm

12,5

1/2"



Code	No.	Sockets	12,5	1/2"	£
2190214	<b>D 19 L-015</b>	⊙ D 19 L 10 12 13 14 15 16 17 18 19 21 22 24 27 30 32	4.3	1	

**IN 19 LKM**

**SCREWDRIVER BIT SOCKET SET 1/2" 15 pieces**

- For in-hex screws (INBUS®), short and long
- In GEDORIT blue sheet steel case
- Dimensions: 320 x 210 x 55 mm
- INBUS® = reg. trademark of Acument GmbH & Co. OHG, 56567 Neuwied

12,5

1/2"



Code	No.	Sockets	12,5	1/2"	£
6129360	<b>IN 19 LKM</b>	⊙ IN 19 5 6 7 8 9 10 12 14 17 ⊙ IN 19 L 5-90 6-90 8-90 10-140 12-140 14-140	3.2	1	

**IN 19 PM**

**SCREWDRIVER BIT SOCKET SET 1/2" 9 pieces**

- For in-hex screws (INBUS®)
- In GEDORIT blue sheet steel case
- Dimensions: 281 x 79 x 35 mm
- INBUS® = reg. trademark of Acument GmbH & Co. OHG, 56567 Neuwied, Germany

12,5

1/2"



Code	No.	Sockets	12,5	1/2"	£
6156250	<b>IN 19 PM</b>	⊙ IN 19 5 6 7 8 9 10 12 14 17	1362	1	

**INX 19 PM**

**SCREWDRIVER BIT SOCKET SET 1/2" 9 pieces**

- For slotted, cross-head and multi-point screws
- In GEDORIT blue sheet steel case
- Dimensions: 281 x 79 x 35 mm

12,5

1/2"



Code	No.	Sockets	12,5	1/2"	£
6150050	<b>INX 19 PM</b>	⊙ INX 19 5 6 8 10 12 ⊕ IKS 19 2 3 ⊖ IS 19 12 16	1.3	1	



1/2"

**ITX 19 PM / ITX 19 B-PM**

**SCREWDRIVER BIT SOCKET SET 1/2" 9 pieces**

- ITX 19 PM: for recessed TORX® head screws
- ITX 19 B-PM: for recessed TORX® head screws with pilot
- In GEDORIT blue sheet steel case
- Dimensions: 281 x 79 x 35 mm
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12,5

1/2"



Code	No.	Sockets	mm	mm	£
6158970	<b>ITX 19 PM</b>	ITX 19 T20 T25 T27 T30 T40 T45 T50 T55 T60	1.2	1	
1394894	<b>ITX 19 B-PM</b>	ITX 19 B T20 T25 T27 T30 T40 T45 T50 T55 T60	1.3	1	

**TX 19 E-09**

**SOCKET SET 1/2" 9 pieces**

- For protruding TORX® screws
- In plastic case
- Dimensions: 200 x 120 x 38 mm
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12,5

1/2"



Code	No.	Sockets	mm	mm	£
6265970	<b>TX 19 E-09</b>	TX 19 E10 E11 E12 E14 E16 E18 E20 E24 3019	1.0	1	

**ITX 19TX-017**

**SCREWDRIVER BIT SOCKET SET 1/2" 17 pieces**

- For protruding and recessed TORX® screws
- In GEDORIT blue sheet steel case
- Dimensions: 320 x 210 x 55 mm
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12,5

1/2"



Code	No.	Sockets	mm	mm	£
6129520	<b>ITX 19TX-017</b>	ITX 19 T20 T25 T27 T30 T40 T45 T50 T55 T60 TX 19 E10 E11 E12 E14 E16 E18 E20 E24	2.8	1	

**ITX 19 LKP**

**SCREWDRIVER BIT SOCKET SET 1/2" 18 pieces**

- For recessed TORX® screws, short and long
- In GEDORIT blue sheet steel case
- Dimensions: 320 x 210 x 55 mm
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12,5

1/2"



Code	No.	Sockets	mm	mm	£
6138510	<b>ITX 19 LKP</b>	ITX 19 T20 T25 T27 T30 T40 T45 T50 T55 T60 ITX 19 L T20 T25 T27 T30 T40 T45 T50 T55 T60	3.2	1	



1/2"