

Crimping pliers - CRIMPFOX-RC 6-M - 1212724

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for uninsulated cable lugs, 0.34 mm² ... 6 mm², indent crimp

Your advantages

- Crimping pliers for uninsulated cable lugs
- Compact and lightweight design
- Marked die stations for precise processing of corresponding cross sections
- Unlockable pressure lock



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 857833
GTIN	4046356857833

Technical data

Dimensions

Length (b)	204 mm
Width (a)	22 mm
Height (c)	76 mm

General

Compression	Indent crimp
Type of contact	Non-insulated cable lugs
Min. cross section	0.34 mm ²
Max. cross section	6 mm ²
Die station	Crimping position 1
Cross section range, metric	0.34 mm ² ... 2.5 mm ²
Cross section range AWG	22 ... 14
Die station	Crimping position 2
Cross section range, metric	4 mm ² ... 6 mm ²

Crimping pliers - CRIMPFOX-RC 6-M - 1212724

Technical data

General

Cross section range AWG	12 ... 10
Weight	500 g

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 11.0	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Crimping pliers - CRIMPFOX-RC 6-M - 1212724


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2022 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>