

REBEL™ RETRIEVAL
SELF RETRACTING LIFELINE

COMPLIANCE AND RESCUE ALL-IN-ONE



TRUSTED, QUALITY FALL PROTECTION

PRODUCT SHEET

REBEL™ RETRIEVAL SRL

COMPLIANCE AND RESCUE ALL-IN-ONE

Designed for confined space applications, the Rebel™ Retrieval SRL adds versatility and convenience to the trusted Rebel™ self-retracting lifeline range. This new model incorporates fall arrest and a built-in emergency retrieval winch for rescue, making it a versatile solution for many job sites. The Retrieval model continues the Rebel™ brand's long history of product performance and value.

Features

- 3-way emergency retrieval system
- Stowable retrieval handle
- Rugged aluminium housing
- Built-in ergonomic carrying handle
- 15m galvanised steel cable lifeline
- Swiveling self-locking snap hook with impact indicator
- Speed sensing all metal brake system
- Internal energy absorption system
- Reserve lifeline system
- Side lifeline exit with ergonomic handle
- High strength, corrosion resistant components
- Swiveling anchorage point
- Self-locking anchorage karabiner
- Optional bracket (3590498) available for easy tripod integration
- Meets or exceeds all applicable industry standards



Ready for Bracket Integration

Swivel Top (Karabiner included)

Ergonomic Carrying Handle

Stowable Retrieval Handle



Specifications:

Part Number: 3591002. **Weight:** 11.9kg. **Pawls:** Stainless Steel. **Main Shaft:** Stainless Steel. **Motor Spring:** Stainless steel. **Fasteners:** Stainless Steel. **Ratchet Arm:** Steel. **Housing:** Aluminium. **Cable:** 5mm galvanised steel. **Cable Bumper:** Urethane. **Swivel Assembly:** Stainless Steel. **Finish:** Powder Coated. **Anchorage Karabiner:** Double action, 17.5mm gate opening, 16kN gate, 22.2kN body, steel. **Snap Hook:** Double action with swivel & fall indicator, 19mm gate opening, 16kN gate, 23kN body, steel. **Lifting & Lowering Ratio:** Gear Ratio 7.4:1. **Capacity:** 140kg. **Compatibility:** Designed for use with PROTECTA tripods, approved harnesses, components or systems, or as recommended by a competent person. **Maximum Arresting Force:** 4kN. **Standards:** EN 360:2002 and EN 1496:2006 class B., OSHA, ANSI Z359.14, & AS/NZS 1891.3. **Country of Origin:** United States. **Special Instructions/Conditions of Use:** Reading user instruction manual prior to use is essential.



Capital Safety - Australia & New Zealand
 Australia: 1800 245 002 | New Zealand: 0800 212 505
www.capitalsafety.com.au
sales@capitalsafety.com.au

