

SGV 8/5

The user-friendly SGV 8/5* is a steam cleaner and wet vacuum cleaner in one. Featuring seven operating modes, an informative display and lots of accessories.



Order no.

1.092-010.0

- 3.5-litre boiler, 3-stage steam flow control, integrated wet vacuum cleaner
- 7 operating modes, hot water/cold water/chemical/self-cleaning function, display
- Floor nozzle, hand nozzle, point jet/crevice/triangle nozzle, round brushes

Technical data

EAN code		4039784846463
Steam pressure	bar	max. 8
Heating output	W	3000
Heat-up time	min	7
Boiler temperature	°C	max. 173
Hot water temperature	°C	70 - 173
Fresh water tank	l	5.6
Dirty water tank	l	5
Cable length	m	7.5
Voltage	V	220 - 240
Frequency	Hz	50 - 50
Colour		anthracite
Weight without accessories	kg	40
Weight incl. packaging	kg	48
Dimensions (L × W × H)	mm	640 × 495 × 965

Equipment

Tank		removable and can be refilled whenever needed
Quantity of steam pipes	Piece(s)	2
Housing		Stainless steel
Steam suction tube	Piece(s) / mm	2 / 505
Floor nozzle	mm	300
Steam/suction hose with steam/suction gun	m	4
Hand nozzle rubber strip	mm	150
Floor nozzle rubber strip	mm	300
Hand nozzle	mm	150
Detail nozzle/adaptor for crevice nozzle	mm	185
Extension for point jet nozzle	mm	140
Triangle nozzle for hand/floor cleaning of corners		■
Small round brush, stainless steel	Piece(s)	1
Small round brush, brass	Piece(s)	1
Small round brush, Pekalon (black)	Piece(s)	1
Push handle		■
Accessory storage (removable)		■
Integrated power cable organiser		■
Display		■
Steam flow control		on handle (three-step)
Safety lock on steam gun		■

This machine requires instruction.

*On/off switch, cold water/vacuuming operation, ecoefficiency mode, steam/hot water/cold water/vacuuming operation, cold rinse function of the machine, detergent/vacuuming operation, self-cleaning function of the machine.



Sustainable and outstanding cleaning performance

- Particularly high steam pressure (8 bar), hot water temperature approx. 70 °C and excellent suction power.
- Removes the most stubborn dirt easily, quickly, efficiently and without the use of chemicals.
- Long-lasting, robust and thus very economical machine.

EASY Operation rotary switch with seven operating modes

- Particularly user-friendly thanks to self-explanatory symbols. No need for time-consuming induction.
- Steams/vacuums with/without ecoefficiency mode and self-cleaning machine.
- On/off switch, cold water, use with detergent, rinse.

Steam/suction hose with steam/suction gun

- Particularly user-friendly rotary and pressure switch for controlling various functions.
- Offers three-stage steam flow control, cold and hot water operation, and simultaneous vacuuming.
- Time-saving: Mode can be adjusted during operation. No need to interrupt the cleaning process.

ACCESSORIES FOR SGV 8/5

1.092-010.0



		Order no.	Description	
STEAM CLEANERS/STEAM VACUUM CLEANERS				
Steam/suction tube, SGV, two pieces, length per piece 505 mm	1	2.889-004.0	The set includes two steam/suction tubes for the SGV steam vacuum cleaner from Kärcher. Length per piece: 505 mm.	■
Brush strips, 300 mm	2	2.889-006.0	Brush strips can be clipped on to the floor nozzle of Kärcher steam vacuum cleaners. Length: 300 mm.	■
Round brush set	3	2.863-011.0	Set consisting of stainless steel, brass and Pekalon round brushes.	■
Floor nozzle 300 mm for SGV steam vacuum cleaner	4	2.889-005.0	Floor nozzle with Pekalon bristles for SGV steam vacuum cleaner. Width: 300 mm.	■
Rubber strip, 300 mm	5	2.889-007.0	Rubber strip for floor nozzle 2.889-005.0.	■
Hand nozzle 150 mm for SGV steam vacuum cleaner	6	2.889-008.0	Hand nozzle for SGV steam vacuum cleaner. One set of brush strips and one set of rubber strips are included in the scope of supply. Width: 150 mm.	■
Brush strips, 150 mm	7	2.889-009.0	Brush strips for hand nozzle 2.889-008.0.	■
Rubber strip, 150 mm	8	2.889-010.0	Rubber strip for hand nozzle 2.889-008.0.	■
1. Point jet nozzle 2. Adapter for round brushes and crevice nozzle for the SGV steam vacuum cleaner, length 185 mm	9	2.889-011.0	The multifunctional adapter can be used as a point jet nozzle for the SGV steam vacuum cleaner. The thread and suction hose port make it possible to attach small round brushes and the crevice nozzle.	■
Crevice nozzle 200 mm for SGV steam vacuum cleaner	10	2.889-028.0	Crevice nozzle for the SGV steam vacuum cleaner from Kärcher. For the extraction of condensate and dirt in joints, crevices and corners after steam cleaning. Length: 200 mm.	■
1. Extension of point jet nozzle 2. Adapter for round brushes for the SGV steam vacuum cleaner, length 140 mm	11	2.889-052.0	Adapter with thread for the SGV steam cleaner for attaching small round brushes. Cleaning in corners and tight spaces is also made easier by the extension of the point jet nozzle.	■
Steam/suction hose with steam/suction gun, length 4 m, for SGV steam vacuum cleaner	12	4.440-009.0	The practical steam/suction hose with steam/suction gun has a particularly user-friendly rotary and pressure switch for controlling various functions. Length: 4 m.	■
Triangle nozzle for cleaning floor corners with SGV	13	2.889-053.0	Practical triangle nozzle for hand and floor cleaning of corners using Kärcher steam vacuum cleaners.	■
Round brush stainless steel set	14	2.863-007.0	Very hard bristles.	□


■ Included in the scope of supply. □ Available accessories.

ACCESSORIES FOR SGV 8/5

1.092-010.0



15



16



17



18



19



20



21



22

		Order no.	Description	
STEAM CLEANERS/STEAM VACUUM CLEANERS				
Round brush brass set	15	2.863-008.0	Hard bristles.	<input type="checkbox"/>
Pekalon round brush set	16	2.863-009.0	Medium-hard bristles.	<input type="checkbox"/>
Pekalon round brush	17	6.907-540.0	Round brush with medium bristles from Pekalon (PEK) and metal threads.	<input type="checkbox"/>
Round brush, blue, Pekalon	18	6.907-587.0	Blue round brush with medium-hard Pekalon (PEK) bristles for Kärcher SGV 6/5 and SGV 8/5 steam vacuum cleaners.	<input type="checkbox"/>
Round brush, green, Pekalon	19	6.907-588.0	Green round brush with medium-hard Pekalon (PEK) bristles for Kärcher SGV 6/5 and SGV 8/5 steam vacuum cleaners.	<input type="checkbox"/>
Round brush, yellow, Pekalon	20	6.907-589.0	Yellow round brush with medium-hard Pekalon (PEK) bristles for Kärcher SGV 6/5 and SGV 8/5 steam vacuum cleaners.	<input type="checkbox"/>
Round brush, red, Pekalon	21	6.907-590.0	Red round brush with medium-hard Pekalon (PEK) bristles for Kärcher SGV 6/5 and SGV 8/5 steam vacuum cleaners.	<input type="checkbox"/>
VACUUMS				
Accessory kits				
Vacuum kit for power tools	22	2.863-112.0	Flexible suction hose (1 m) including adapter for connection to the exhaust air vent of power tools (e.g. jigsaws, grinders, drills, planes, etc.), for dirt-free DIY.	<input type="checkbox"/>

■ Included in the scope of supply. □ Available accessories.