



Socket

52

Product no. 03030025
GTIN 4018754005970
Model 52 25



Label. 1/2 " Socket Size 25mm L.42mm

Properties.

- hex with AS-Drive profile
- 1/2" internal square drive
- HPQ® high performance steel, chrome-plated
- DIN 3124 / ISO 2725-1 / ASME B 107.5M / DIN EN 3709


Technologies and features.



High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

Technical drawing.



Technical attributes.

Drive profile	hex AS-Drive
Square drive inner (inch)	1/2 "
d1	33,2 mm
d2	26 mm
d3	22 mm
DIN	DIN 3124 / ISO 2725-1, ASME B 107.5M, DIN EN 3709
Length mm (L)	42 mm
Size [mm]	25 mm
t1	18,5 mm
t2	24,6 mm

Logistics data.

Depth mm (IFS)	42
Width mm (IFS)	34
Height mm (IFS)	34
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	93
Width (packaged, mm)	75
Height (packaging, mm)	42
Volume (packaged, dm3)	0.29295 dm3
Product no.	03030025
Weight (gross, kg)	0,640
Weight PAP (kg)	0,000
Weight PVC (kg)	0,006
GTIN	4018754005970
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	5
Weight (g)	128 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
03030008	52 8	1/2 " Socket Size 8mm L.38mm	4018754005802
03030009	52 9	1/2 " Socket Size 9mm L.38mm	4018754005819
03030010	52 10	1/2 " Socket Size 10mm L.38mm	4018754005826

03030011	52 11	1/2 " Socket Size 11mm L.38mm	4018754005833
03030012	52 12	1/2 " Socket Size 12mm L.38mm	4018754005840
03030013	52 13	1/2 " Socket Size 13mm L.38mm	4018754005857
03030014	52 14	1/2 " Socket Size 14mm L.38mm	4018754005864
03030015	52 15	1/2 " Socket Size 15mm L.38mm	4018754005871
03030016	52 16	1/2 " Socket Size 16mm L.38mm	4018754005888
03030017	52 17	1/2 " Socket Size 17mm L.38mm	4018754005895
03030018	52 18	1/2 " Socket Size 18mm L.38mm	4018754005901
03030019	52 19	1/2 " Socket Size 19mm L.38mm	4018754005918
03030020	52 20	1/2 " Socket Size 20mm L.42mm	4018754005925
03030021	52 21	1/2 " Socket Size 21mm L.42mm	4018754005932
03030022	52 22	1/2 " Socket Size 22mm L.42mm	4018754005949
03030023	52 23	1/2 " Socket Size 23mm L.42mm	4018754005956
03030024	52 24	1/2 " Socket Size 24mm L.42mm	4018754005963
03030025	52 25	1/2 " Socket Size 25mm L.42mm	4018754005970
03030026	52 26	1/2 " Socket Size 26mm L.42mm	4018754005987
03030027	52 27	1/2 " Socket Size 27mm L.45mm	4018754005994
03030028	52 28	1/2 " Socket Size 28mm L.45mm	4018754006007
03030030	52 30	1/2 " Socket Size 30mm L.45mm	4018754006021
03030032	52 32	1/2 " Socket Size 32mm L.47mm	4018754006038
03030034	52 34	1/2 " Socket Size 34mm L.47mm	4018754006045
03030036	52 36	1/2 " Socket Size 36mm L.52mm	4018754283675

GTIN.

**STAHLWILLE Eduard Wille GmbH**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal