



"PanelSeT S3D seismic plain door with mount.plate - H1200xW800xD400 - IP65 - IK10"

Local distributor code:

402657860 NSYS3D6G12840P

EAN Code: 3606480793998

Main

Range	PanelSeT	
product name	S3D 6G	
Enclosure application	Seismic	
Product or component type	Enclosure	
Enclosure nominal height	1200 mm	
Enclosure nominal width	800 mm	
Enclosure nominal depth	400 mm	
Door type	Plain	
Mounting plate description	Reinforce	
Enclosure mounting	Wall mounted	
Device composition	1 x body 1 x door 1 x lock 2 x fixing bracket 2 x cable gland plate 1 x mounting plate 1 x earthing components door and lock	
Continuity of earth	Earthing connection between body and door	

Complementary

Body type	Gutter-shaped front rail Single piece body	
Number of doors	Front face: 1 door(s)	
Door opening side	Right (120 °)	
Lock type	3-point closure	
Type of keylock	405E	
Type of operating handle	Swing handle	
Accessibility for operation	Front	
Removable parts	Cable gland plate by screws	
Material	Steel	
Thickness	Body: 2 mm Door: 2 mm Cable gland plate: 1.5 mm	
Surface finish	Epoxy-polyester powder	
Colour	Grey (RAL 7035)	
Net weight	89 kg	

Environment

Surface treatment	87 % decontaminable painting conforming to NF T 30-501.	
Standards	IEC 62208 EDF CRT 91 C 112 00	
IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK10 conforming to IEC 62262	
Seismic performance	Seismic tests 6G conforming to EDF CRT 91 C 112 00	

Packing Units

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	45.000 cm
Package 1 Width	88.000 cm
Package 1 Length	127.000 cm
Package 1 Weight	86.200 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	2
Package 2 Height	102.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	184.400 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	812	

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

☼ Repack and remanufacture		
Take-back	No	