



ScotchCode™

SDR STD

Data Sheet



Product Description

Dispenser

The ScotchCode STD Tape Dispenser is a compact, carry-along dispenser with ten refillable compartments, which hold eight-foot rolls of non-smear polyester tape. Used for marking binder groups, wire or cable, the tapes 'high tack', acrylic adhesive resists solvents, oil and water and adheres firmly to insulation surfaces. An end loop hooks the dispenser easily to a tool pouch or belt. Dispensers can be ordered empty or filled with 10 rolls of pre-printed numbered or coloured tapes.

Refill Rolls

This aggressive adhesive system, combined with the flexible polyester film backing, provides a thin, conformable tape that is durable and will hold up in most industrial electrical applications. The smooth surface of this tape allows dirt and grime to be easily wiped off, providing text legibility even after extended exposure to a build up of contamination.

Applications

Marking all types of wire and cable including power, control, fibre optic, electronic, telecommunications, and instrumentation.

Phase identification on large or small gauge wire or cable.

Identification of terminal blocks, terminal strips, and wire in panel boards or switchgear.

Automotive applications on tubing, hoses and replacement parts.

Technical Information

UV resistant

Operating temperature range

-40°C to + 121°C

Application temperature

0°C to + 49°C

Characters per roll

790

Tape dimensions

Width 5.46mm

Length 2.4m

Thickness 0.08mm

Key Features and Benefits of STD Tape Dispenser

Feature	Benefit
Compact design	Easy to handle
Hangs from a tool belt	Convenient
Provides contamination protection around the wire markers	Markers stay clean and dry
Can be custom filled to meet specific project requirements	No waste
Dispenses only the desired length	Prevents waste
Holds ten rolls of SDR wire marking tape	Compact

Presentation

Presentation Reference	Description
STD	Dispenser only
STD 0-9	Dispenser filled with 10 rolls of numbered tape (one each of 0-9)
STD Y/G	Dispenser filled with 10 rolls of coloured tape (one each of blue, brown, green, grey, orange, red, violet, white, yellow and yellow/green)
SDR	Refill rolls packed by 10

Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law. If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

3M and ScotchCode are trademarks of the 3M Company. Printed in the UK.
© 3M United Kingdom PLC, 2003

Electrical Products Group

3M United Kingdom PLC

Sales Office

PO Box 393

Bedford MK41 0YE

Telephone: 01234 229462

Fax: 01234 229433

3M Ireland

Sales Office

3M House, Adelphi Centre, Upper Georges Street

Dun Laoghaire, Co Dublin, Ireland

Telephone: 353 1 280 3555

Fax: 353 1 280 3509

3M United Kingdom PLC

Head Office

3M Centre, Cain Road

Bracknell, Berkshire RG12 8HT

Telephone: 01344 858000

Fax: 01344 858758