



Mini GaN Wall Chargers with Display & Cable

PN: 30238, 30239, 30240

Delivering up to 140W across up to four ports, the mini GaN chargers power laptops, tablets, and phones simultaneously.

Its TFT display shows real-time voltage and current. With PPS and GaN technology, it charges efficiently, runs cool, and ensures safety.

Interchangeable EU, UK, and US plugs make it perfect for travel.

- Compact wall charger with USB-C® Power Delivery 3.2 and Quick Charge 3.0
- Integrated TFT touchscreen display shows real-time charging performance
- PPS (Programmable Power Supply) support for optimal charging efficiency
- Two USB-C PD 3.2 ports up to 140W each (PN: 30240)
- One USB-A QC 3.0 port up to 30W
- 100cm USB-C to USB-C cable included (up to 480Mbps) for charging and data transfer
- Charge up to four devices simultaneously – laptop, tablet, and phone
- Powered by advanced GaN technology for compact size and reduced heat
- Multi-region plugs (EU, UK, US) for easy travel
- Fireproof PC material ensures safe, durable operation
- Built-in overcurrent, overvoltage, over-temperature and short-circuit protection
- Universal input 100–240V for global compatibility
- Plastic-free packaging
- 2-year limited warranty



Support
PD 3.2 & QC 3.0



TFT
Display



Multi-Plug
Included



USB-C Cable
Included



PN: 30238, 30239, 30240

Product Specifications

- Fireproof PC material
- Input: 100V – 240V 50/60Hz
- Charging Protocols:
 - **USB-C:** PD 3.2 (PPS supported)
 - **USB-A:** QC 3.0
- Storage Temperature: -25 °C to +40 °C
- Operating Temperature: 0 °C to +25 °C
- Operating Humidity: 20% -80%
- RoHS REACH: Yes
- Short circuit, Over-voltage, Over-current, Over-temperature protections

1m USB-C to
USB-C Cable
up to 480Mbps



TFT Display

Touch Button

USB Ports



US plug




UK plug



EU plug

Display modes

Opening sequence



PN	# Devices	USB-C	USB-A	Max Total Output	Power Delivery	Q.C.	Cable
30238	3	2 x 65W	1 x 20W	65W	PD 3.2	3.0	60W USB-C to USB-C – 1m
30239	3	2 x 100W	1 x 30W	100W	PD 3.2	3.0	100W USB-C to USB-C – 1m
30240	4	2 x 140W + 1 x 40W	1 x 30W	140W	PD 3.2	3.0	140W USB-C to USB-C – 1m


Languages

Front of pack: English (Product description also in French)

Back of pack: English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, Korean, Japanese

Quick Installation Languages

English, French, German, Traditional Chinese, Technical support text: English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, Korean, Japanese



Reorder No.	Description	Tariff Code	Barcode	EAN-128	EAN-14
30238	Verbatim Mini GaN Charger 65W with Display + 60W USB-C to USB-C Cable (Charge & Data Transfer) – Grey	85366990	0023942302384	(02)00023942302384(37)06(91)864 (02)00023942302384(37)24(91)864	20023942302388 50023942302389
30239	Verbatim Mini GaN Charger 100W with Display + 100W USB-C to USB-C Cable (Charge & Data Transfer) – Grey	85366990	0023942302391	(02)00023942302391(37)06(91)864 (02)00023942302391(37)24(91)864	20023942302395 50023942302396
30240	Verbatim Mini GaN Charger 140W with Display + 140W USB-C to USB-C Cable (Charge & Data Transfer) – Grey	85366990	0023942302407	(02)00023942302407(37)06(91)864 (02)00023942302407(37)24(91)864	20023942302401 50023942302402

Reorder No.	30238	30239	30240
Product Dimensions L x W x H	58 x 31 x 58 mm	68 x 31 x 68 mm	71.5 x 36.5 x 71.5 mm
Product Weight incl Plugs + Cable (approx)	199 g	268 g	348 g
Units per Pack	1	1	1
Pack Dimensions L x W x H	110 x 55 x 116 mm	110 x 55 x 123 mm	110 x 55 x 129.5 mm
Pack Weight (approx)	284 g	360 g	438 g
Packs per Inner Carton (MOQ)	6	6	6
Inner Carton Dimensions L x W x H	355 x 125 x 140 mm	355 x 150 x 145 mm	355 x 15 x 150 mm
Inner Carton Weight (approx)	2000 g	2450 g	2970 g
Packs per Outer Carton	24	24	24
Outer Carton Dimensions L x W x H	375 x 275 x 305 mm	375 x 275 x 315 mm	375 x 275 x 325 mm
Outer Cartons Weight (approx)	8000 g	9800 g	1190 g
Outer Cartons per Layer	10	10	10
Layers per Pallet	3	3	3
Packs per Pallet	720	720	720

Pack Content

- GaN Charger
- USB-C to USB-C Cable (1m)
- EU, UK and US plug Adapter
- Quick Start Guide