

Features

- Jaws move in parallel throughout use.
- Nylon jaw inserts prevent damage to material.
- Long-lasting return spring.
- Zinc-plated handles with detailing for added grip.

RS PRO Nylon Jaws Flat Nose Parallel Plier 140 mm

RS Stock No.: 0434622



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Nylon Jaws Flat Nose Parallel Plier

Engineered for damage-free working. Designed with nylon jaw inserts to protect your workpiece from marks or damage. Jaws move in parallel to hold material in a secure grip. Perfect for working with malleable materials and or fixings with polished aesthetic finishes.

Benefits

- Ideal for holding, gripping and manipulating without damage.
- Work without fear of marking your workpiece.
- Parallel jaws grip securely along their whole length.
- Manipulate, straighten and remove kinks in wire and other soft materials.
- Easier handling of parts due to return spring.
- Built to last, with a robust construction and rust-resistant finish.

Applications

The essential tool for holding and bending fine wire and other soft materials. Ideal for:

- Design engineers.
- Model builders
- Horologists.

General Specifications

Plier Type	Nylon Jaws Parallel Plier Return Spring
Number of Pieces	1
Overall Length	140 mm
Cutting Capacity	N/A
Material	Steel jaws with nylon inserts, zinc-plated steel handles
ESD Safe	No
Jaw Length	25 mm usable jaw length
Jaw Opening	10mm
Jaw Width	8 mm
Non Sparking	No
Height Safe	No

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Jaw Opening	Parallel	Overall Length
0606317	RS PRO	CENTRE CONDUCTOR CUTTING NIPPER	Up to 25 mm (Duct Rod Ø)	No	110 mm
0606320	RS PRO	Bullet & Snap Connector Insert Tool	46mm	No	145mm
0606319	RS PRO	Spanner Quick Grip	25 mm Max	No	135mm
0606316	RS PRO	Security Crimping and Cutter Plier	0.9mm (Ø cables)	No	212mm
0434623	RS PRO	Snipe Nose Serrated Jaws Parallel Plier	10mm	Yes	125mm
0606318	RS PRO	Snipe Nose Smooth Jaws Parallel Plier	10mm	Yes	125mm
0434621	RS PRO	Fine Nose Round Jaws Parallel Plier	11mm	Yes	125mm
0606312	RS PRO	Fine Clamping Plastic Jaws Parallel Plier	20mm	Yes	168mm
0434622	RS PRO	Flat Nose Nylon Jaws Parallel Plier	10mm	Yes	140mm
0441178	RS PRO	Side Cutter Parallel Plier for Hard Wire 125mm	10mm	Yes	125mm
0606314	RS PRO	Side Cutter Parallel Plier for Hard Wire 160mm	14mm	Yes	167mm
0606313	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm	8mm	Yes	140mm
0434617	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm, w/ Grip Handle	8mm	Yes	140mm

