



1535

Air

Carry-On Case

Peli™ Air cases are the toughest and lightest cases Peli has to offer. Designed with a super-light proprietary HPX² polymer construction, each Peli Air case is up to 40 percent lighter than an average polymer case, yet still extremely durable. Peli Air cases are waterproof, crushproof, and dustproof.

The Peli 1535 Air Case provides protection for a wide variety of gear, from camera equipment to camping kits. It is available with foam, without foam, padded dividers, or TrekPak dividers. The Peli 1535 Air Case is the maximum airline carry-on size, so you can travel with your sensitive gear close at hand. This Peli Air case will lighten the load, while protecting your valued possessions.

(Check with your airline for exact measurement requirements)

- Crushproof, watertight, and dustproof (IP67)
- Super-light proprietary HPX²™ polymer – up to 40% lighter than traditional cases
- Press and Pull™ latches for secure closure
- Retractable extension trolley handle for easy transport
- Quiet rolling stainless steel bearing wheels
- Foldable, ergonomic rubber handles
- User-customizable Pick N Pluck™ foam interior
- Waterproof O-ring seal
- Automatic pressure equalization valve – balances interior pressure, keeps water out
- Stainless steel padlock protectors and hardware
- Business card holder for personal or professional ID
- MIL-SPEC certified for professional-grade protection
- Use as dry box, lock box, suitcase, or toolbox
- Ideal for cameras, lenses, laptops, and tools
- Peli™ Limited Lifetime Guarantee



CONFIGURATIONS



1535
Standard



1535NF
No Foam



1535WD
With Padded Dividers



1535TP
With TrekPak Divider System



1535WF
With Foam



1535AIRTPF
TrekPak / Foam Hybrid



1535AV
Universal Camera

DIMENSIONS

Interior (L×W×D)	20.39 x 11.20" x 7.21 (51.8 x 28.4 x 18.3 cm)
Exterior (L×W×D)	21.96 x 13.97" x 8.98 (55.8 x 35.5 x 22.8 cm)
Lid Depth	2.00" (5.1 cm)
Bottom Depth	5.21" (13.2 cm)
Total Depth	7.21" (18.3 cm)
Int Volume	0.95 ft ³ (0.027 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Proprietary Polypropylene Blend
-------------	---------------------------------

Latch	ABS
O-Ring	EPDM
Purge Body	ABS
Purge Vent	Hi-Flow Gore-Tex 3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Orange	 Silver	 White
 Yellow	 Graphite	 Sage / Gray	 French Blue
 OCP Tan	 Hunter Green		

WEIGHT

Weight With Foam	9.98 lbs (4.53 kg)
Weight Empty	8.69 lbs (3.94 kg)
Buoyancy	64.80 lbs (29.39 kg)
Weight With TrekPak / Foam Hybrid	11.91 lbs (5.4 kg)


TEMPERATURE

Minimum Temperature	0°F (-17.8 °C)
Maximum Temperature	140°F (60 °C)

OTHER

Wheels	2
---------------	---

ACCESSORIES

 1535AirFS 5 pc. Replacement Foam Set	 1535AirDS Padded Divider Set	 1535TP-KIT TrekPak Case Divider Kit	 1510TPDIV Extra TrekPak Dividers	 1506TSA TSA Lock
 1500D Desiccant Silica Gel	 1535MP EZ-Click™ MOLLE Panel	 RucPac-Pro-1 RucPac Pro Hardcase Backpack Conversion	 RucPac-normal RucPac Standard Hardcase Backpack Conversion	 AIRHANDL EZ-Pull Multi-Stage Air Handle



1535TPDIV
Extra TrekPak Dividers

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com

Document created on 08-19-26