

# Stronghold+ (GM007\*)

extended cuff · AQL 0.65 · enhanced chemical splash protection  
silicone free · purple · medical grade · heavy weight · nitrile  
unique Unigloves formulation · single use gloves

### Physical Specifications:

Material: Nitrile (latex free)  
Colour: Purple  
Length: 300 mm  
Weight: 7.3 g  
Thickness: 0.12 mm  
Finish: Powder free, chlorinated  
Fit: Ambidextrous  
Sterile: No

### Order Codes and Size Information:

GM0071 | Extra small  
GM0072 | Small  
GM0073 | Medium  
GM0074 | Large  
GM0075 | Extra large

### Packaging:

Each dispenser box contains 100 gloves  
Each case contains 10 dispenser boxes

### Classification:



For more about the **Advanced** range, please **click on the image**



### Features

- Free from silicone
- Tested to EN374
- Tested to ASTM D6978-05
- Extended cuff (300mm glove length)
- AQL 0.65 and EN455 parts 1-4
- Tested to EN1186
- Nitrile formulation conforms to the hand during use
- Beaded cuff
- Manufactured with textured palms and fingers
- Heavy-weight construction
- Touchscreen compatible

### Benefits

- Silicone free formulation means no finger marks on metal and glass surfaces
- Resistant to a range of chemicals
- Resistant to a range of cytotoxic drugs when tested to ASTM D6978-05
- Extended cuff helps prevent liquids getting into the glove when working in wet conditions and provides additional protection from chemical splashes
- Meets medical standards + ultra-low hole level (exceeds medical standards for pinholes)
- Suitable for contact with all food types
- Nitrile formulation conforms to the hand during use for a more comfortable fit
- Beaded cuff provides extra strength during donning and helps prevent liquid roll back
- Textured palms and fingers provide improved grip, particularly when working in wet or oily conditions
- Heavy-weight construction is tough, durable and long lasting
- Suitable for use with mobile and tablet displays without removing gloves

### Sectors

- Aerospace • Chemical manufacture and use • Dentistry
- Dental hygiene • Electronics • Engineering • Food processing
- Healthcare • Laboratory work • Manufacturing and assembly
- Pharmaceutical work • Printing



**UNIGLOVES UK**  
Registered in England No: 4010200  
VAT registration 791817787

📍 3 Ambley Green, Gillingham Business Park,  
Gillingham, ME8 0NJ, UK  
☎ +44 (0)800 049 6602  
✉ enquiries@unigloves.co.uk  
🌐 unigloves.co.uk

**UNIGLOVES GERMANY**  
Arzt- & Klinikbedarf  
Handelsgesellschaft mbH

📍 Camp-Spich-Straße 71  
D-53842 Troisdorf-Spich,  
☎ +49 (0) 2241-9323-0  
✉ unigloves@unigloves.de  
🌐 unigloves.de

