

## Features

- Engineered to deliver efficient cutting through both wood and metal.
- Manufactured from premium M2 High Speed Steel, this blade is optimised for slicing soft nails, mild steel, and non-ferrous metal components embedded in wood.
- 150mm length providing up to 100mm cutting capacity.

## Reciprocating Saw Blade –Wood & Metal 150 x 19 x 0.9mm –Fast Cut

RS Stock No.: 0757831



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Reciprocating Saw Blade

0757831 Wood & Metal Reciprocating Saw Blade is engineered to deliver efficient cutting through both wood and metal. Manufactured from premium M2 High Speed Steel, this blade is optimised for slicing soft nails, mild steel, and non-ferrous metal components embedded in wood. With a standard 150mm length providing up to 100mm cutting capacity.

- *Manufactured with 6150 Chromium-Vanadium Spring Steel & M2 High Speed Steel teeth*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Wood With Nails, Wooden Pallets & Pipes*
- *Supplied in 5pc Packs*

## General Specifications

<b>Tooth Design</b>	Side Set, Milled
<b>Type</b>	Reciprocating Saw Blade
<b>Teeth Spacing</b>	2.5mm
<b>TPI</b>	10
<b>Thickness</b>	0.9mm
<b>Max Cut Depth</b>	100mm
<b>Cut Type</b>	Fast Cutting
<b>Blade Material</b>	M2 High Speed Steel
<b>Body Material</b>	6150 Chromium-Vanadium Spring Steel
<b>Fitting</b>	S-Shank 1/2"
<b>Length</b>	150mm
<b>Width</b>	19mm

Stock No.	Cut Type	Thickness	Length	Width
XXX-XXXX 0757831	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757832	Coarse Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757833	Fast Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757834	Coarse Cutting	1.25mm	300mm	19mm

## Approvals

### Declarations

REACH DoC

## Similar Products

Stock No.	Brand	Product Name	Cut Type	Thickness	Length	Width
XXX-XXXX 0757831	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757832	RS PRO	Reciprocating Saw Blade	Coarse Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757833	RS PRO	Reciprocating Saw Blade	Fast Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757834	RS PRO	Reciprocating Saw Blade	Coarse Cutting	1.25mm	300mm	19mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories