

Features

- RS PRO and Little Giant dual-branded professional solution
- Aerospace-grade aluminium construction
- Multi-position design for maximum versatility
- Redesigned Double-Lock hinge mechanism
- Spring-assisted Rapid-Lock adjustment system
- Flared leg design for enhanced stability
- Tip & Glide wheels for easy transportation
- Up to 24 ladder configurations in one product
- Compatible with Tetra Ladder System accessories
- Suitable for intensive professional use
- Lightweight design for easier handling
- Rated to 150kg maximum load capacity

RS PRO by Little Giant®

Velocity Series 2.0 Multi-Purpose Ladder



RS PRO® is the own brand of RS. Combining quality, choice and value, RS PRO products are professionally approved and trusted by engineers worldwide. Little Giant® is a registered trademark of Little Giant Ladder Systems.

Product Description

The RS PRO by Little Giant® Velocity Series 2.0 Multi-Purpose Ladder is a professional-grade, multi-position aluminium ladder designed for demanding industrial, maintenance and trade applications. Combining the trusted reliability of RS PRO with Little Giant's innovative ladder technology, the Velocity Series 2.0 provides exceptional versatility, safety and productivity.

The ladder can be configured in multiple working positions including:

- A-Frame Ladder
- Extension Ladder
- Staircase Ladder
- 90° Wall Ladder
- Trestle & Plank Scaffolding (with compatible accessories)

Constructed from aerospace-grade aluminium and featuring a redesigned Double-Lock Hinge and Rapid-Lock adjustment system, the Velocity Series 2.0 enables fast setup, easy transportation and stable operation across a wide range of tasks.

Standards and Compliance

Standard	EN131-4:2020 Professional
Maximum Load Capacity	150kg
Usage Classification	Professional / Intensive Use
Material	Aluminium

Applications

Electrical installation
Facilities maintenance
Construction
Building services
Warehousing
Manufacturing environments
Property maintenance
Decorating and refurbishment
Trade professionals

Technical Specification

Brand	RS PRO by Little Giant®
Product Type	Multi-Purpose Ladder
Material	Aluminium
Ladder Style	Multi-Position
Maximum Working Load	150kg
Rung Depth	25mm
Distance Between Rungs	297mm
Colour	Aluminium/Silver
Wheels	Integrated Tip & Glide Wheels
Configuration Options	A-Frame, Extension, Staircase, 90°, Trestle & Plank

Product Dimensions

Stock No.	Rungs / Sections	Last Climbing Height (mm)	Approx. Working Height (mm)	Extended Length (mm)	Closed Length (mm)	Weight (kg)
889692	3 x 4	2360	4310	2110 – 3330	1090	12.3
889693	4 x 4	3530	5480	2720 – 4550	1400	14.7
889694	5 x 4	4720	6670	3330 – 5770	1689	18.6
889695	6 x 4	5890	7840	3940 – 6990	1990	23.5

Product Dimensions

Stock No.	Max Step Height (mm)	Approx. Working Height (mm)
889692	3 x 4	2840
889693	4 x 4	3420
889694	5 x 4	3980
889695	6 x 4	4570

Storage Dimensions

Stock No.	Width (mm)	Depth (mm)
889692	775	200
889693	883	220
889694	997	220
889695	1118	220

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories



Safety Note

Always inspect ladder equipment before use and follow all applicable workplace safety procedures. Ensure the ladder is fully locked into position before climbing.