



PRODUCT-DETAILS

M12-C103

M12-C103 Cable



360°

General Information	
Extended Product Type:	M12-C103
Product ID:	2TLA020056R4000
EAN:	7350024452471
Catalog Description:	M12-C103 Cable
Long Description:	M12-C103 is a shielded cable with a straight M12-8 female connector and a free end. The eight conductors have a cross section of 0.34 mm2. The jacket is made of black PVC. The length of the cable is 10 meters.
Display Name:	M12-C103

Ordering	
Minimum Order Quantity:	1 piece
Customs Tariff Number:	8544429090

Popular Downloads	
Data Sheet, Technical Information:	2TLC010077L0201

Instructions and Manuals:	2TLC010077L0201
Marketing Video:	9AKK10103A4645 2TLC010018N0201

Dimensions

Product Net Depth / Length:	10 m
Product Net Height:	15 mm
Product Net Width:	15 mm
Product Net Weight:	0.478 kg

Technical

Suitable For:	Orion1-4-14-015-B Orion1-4-14-030-B Orion1-4-14-045-B Orion1-4-14-060-B Orion1-4-14-075-B Orion1-4-14-090-B Orion1-4-14-105-B Orion1-4-14-120-B Orion1-4-14-135-B Orion1-4-14-150-B Orion1-4-14-165-B Orion1-4-14-180-B Orion1-4-30-015-B Orion1-4-30-030-B Orion1-4-30-045-B Orion1-4-30-060-B Orion1-4-30-075-B Orion1-4-30-090-B Orion1-4-30-105-B Orion1-4-30-120-B Orion1-4-30-135-B Orion1-4-30-150-B Orion1-4-30-165-B Orion1-4-30-180-B Orion2-4-K2-050-B Orion2-4-K3-080-B Orion2-4-K4-090-B Orion2-4-K4-120-B Orion3-4-K1C-050-B Orion3-4-K2C-080-B Orion3-4-K2C-090-B Orion3-4-K2C-120-B Orion2-4-K2-050-E Orion2-4-K3-080-E Orion2-4-K4-090-E Orion2-4-K4-120-E Orion3-4-K1C-050-E Orion3-4-K2C-080-E Orion3-4-K2C-090-E Orion3-4-K2C-120-E Magne 2A Magne 2B Adam OSSD-Info M12-8 Adam OSSD-Reset M12-8 JSTD25K JSTD25H OCB--1A OCB-2A
---------------	--

Material Compliance

Conflict Minerals Reporting Template (CMRT):	9AKK108467A5658
REACH Declaration:	2CMT2022-006480
RoHS Declaration:	2CMT2022-006499
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA:	2CMT2023-006522
WEEE B2C / B2B:	Business To Business
WEEE Category:	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

cULus Certificate:	2TLC172257D0201
Declaration of Conformity - CCC:	No declaration needed
Declaration of Conformity - CE:	No declaration needed
Declaration of Conformity - UKCA:	No declaration needed
UL Certificate:	2TLC172257D0201

External Classifications and Standards

E-Number (Sweden):	3861426
ETIM 9:	EC001855 - Sensor-actuator patch cord
ETIM 10:	EC001855 - Sensor-actuator patch cord
Object Classification Code:	W
UNSPSC:	26121603
eClass:	V11.0 : 27060313

Categories

Products > Low Voltage Products and Systems > Control Products > Safety Products > Cables and Connectors

Products > Low Voltage Products and Systems > Control Products > Safety Products > Optical Safety Devices

Products > Low Voltage Products and Systems > Control Products > Safety Products > Safety Sensors, Switches and Locks



360°

