



1550 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Pelican™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Pelican cases have survived. Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- Personalized nameplate service available
- **Watertight, crushproof, and dustproof**
- 2 level Pick N Pluck™ with convoluted lid foam
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Comfortable rubber over-molded handle
- Easy open double-throw latches
- Lifetime Guarantee of Excellence
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Stainless steel hardware and padlock protectors



CONFIGURATIONS



1550
Standard



1550NF
No Foam



1550TP
With TrekPak Divider System



1554
With Padded Dividers



1550WF
With Foam

DIMENSIONS

Interior (L×W×D)	18.63 x 14.18" x 7.72 (47.3 x 36 x 19.6 cm)
Exterior (L×W×D)	20.66 x 17.20" x 8.40 (52.5 x 43.7 x 21.3 cm)
Lid Depth	1.75" (4.4 cm)
Bottom Depth	5.87" (14.9 cm)
Total Depth	7.62" (19.4 cm)
Int Volume	1.18 ft ³ (0.033 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLORS

 Black	 Orange	 Silver	 Yellow
---	--	--	--

WEIGHT

Weight With Foam	11.90 lbs (5.4 kg)
Weight Empty	10.58 lbs (4.8 kg)
Buoyancy	69.89 lbs (31.7 kg)
Master Pack Weight	28.35 lbs (12.9 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	210°F (98.9 °C)


CERTIFICATIONS

IP67
MIL C-4150J
Def Stan 81-41
ATA 300

OTHER

Master Pack	2
Nameplate	yes
Military	yes

ACCESSORIES

				
1551 4 pc. Replacement Foam Set	1552 Pick N Pluck™ Sections Only (set of 2)	1553 Replacement O-ring	1555 Padded Divider Set	1550PF Special Application Panel Frame
				
1550TPKIT TrekPak Case Divider Kit	1510TPDIV Extra TrekPak Dividers	1507 Quick Mounts - set of 4	1506TSA TSA Lock	1500D Desiccant Silica Gel



1500CI
Corrosion Intercept Kit

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 05-09-25