



Handling protection

ULTRANE 550



Unbeatable for fingertip precision

SPECIFIC ADVANTAGES



Comfort

- Great dexterity, due to the gloves reduced thickness
- Added comfort, due to the seamless knit lining Absorption of perspiration ensured by the cellular structure of the polyurethane



Durability

- Suitable for long-term wear : excellent abrasion resistance



Skin protection

- Free of harmful substances: OEKO-TEX® STANDARD 100
- Contains traces of DMF in compliance with occupational exposure limits



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Additional benefits

- Available in vending machine packaging

EN388



4131X

CATEGORY 2



DEXTERITY

EN ISO 21420:
5/5



INDUSTRIES

- Automotive/mechanical industry
- Electronics
- Cosmetics and Pharmaceutical industry

APPLICATIONS

- Electronic component assembly (displays, LEDs, etc.)
- High-frequency antennae riveting
- Microprocessor handling
- Cosmetics preparation
- Medicine manufacturing
- Fitting small screws and fasteners
- Intricate assembly
- Sorting small parts



Handling protection

ULTRANE 550

LEGENDS

EN388						MECHANICAL HAZARDS
						PERFORMANCE LEVELS (X = NOT TESTED)
4	1	3	1	X		
0-4	0-5	0-4	0-4	A-F	P	
						Impact protection (optional)
						Cut resistance according to ISO 13997
						Puncture resistance
						Tear resistance
						Blade cut resistance
						Abrasion resistance

PRODUCT DETAILS

Interior finish	Seamless textile support
Gauge	13
Exterior finish	Ventilated back
Material	Polyurethane
Cuff characteristic	Knitted Cuff
Colour.s	White
European sizes	5 6 7 8 9 10
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	2.4E+11 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	7.4E+9 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 10 pairs/bag 100 pairs/carton
-----------	--

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/05/18/0965 update 01 05/01/2023
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE

Edit 03/12/2024