



Multi Purpose



Oil



Light Duty

Multipurpose, abrasion-resistant, nitrile-coated safety gloves offering oil resistance

- **Heightened dexterity:** These flexible high-dexterity work gloves feature a lightweight, seamless knitted dark grey polyester liner and elasticized knitwrist dipped into black straight nitrile coating
- **Optimized durability:** Thanks to their black nitrile coating, EDGE[®] 48-128 protective gloves grant better abrasion and oil resistance, grip and cushioning than light and mediumweight knitted cotton gloves
- **Improved features:** EDGE[®] 48-128 industrial gloves come in a dark color that shows dirt contamination less quickly and are the practical choice for light applications where oil is present
- **Food handling compliance:** Made with FDA-compliant materials, these food gloves are safe for food packaging



Industries

- Automotive
- Machinery and Equipment

Applications

- Assembly of small parts
- General handling
- Packaging
- Quality control

Key Features

- **Seamless design:** For lightweight, flexible and dexterous work gloves
- **Nitrile coating:** Increased mechanical performance, grip and comfort
- **Dark-colored:** Reusable high-quality work gloves that conceal dirt

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



4121A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-128	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Polyester Cuff Style: Knitwrist	13	6, 7, 8, 9, 10	220-270 mm; 8.66-10.63 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699