TRICOFLEX

LASER INDUSTRIE

made in EUROPE



Sprayers for Industry

acidic, neutral, and basic Products



Sprayers
LASER INDUSTRIE

High-performance and reliable sprayers
manufactured in France, in Villefranche-sur-Saône since 1991

Gachette 1L

Handheld Sprayers –
No Pre-Pressurisation Required



JOINTS NITRILE SEALS

Watering & Plant care

water, fertilisers

- cuve translucide

6 7 8

F1 Viton®

Handheld Sprayers –
No Pre-Pressurisation Required



JOINTS VITON SEALS

Solvent-Based Hydrocarbon Products

Insecticides, paint strippers

- graduated gauge

4 5 6 7 8

Laser 2 Viton®

Pre-Pressurised Sprayers



JOINTS VITON SEALS

Neutral or Mildly Acidic Products

Paint strippers, wood and framework treatment, disinfection, pest control, tar removers

- handle with lock button for continuous spraying
- translucent graduated tank with a wide opening for easy filling
- anti-theft nozzle
- safety valve set at 3 bar

4 5 6 7 8

Exel 10

Pre-Pressurised Sprayers



JOINTS VITON SEALS

Exel 7

Diluted Acidic Products

Deactivators, solvent-based products

- non-locking lance handle, in compliance with European standards
- integrated filter
- translucent graduated tank
- 30cm lance
- adjustable nozzle (from straight jet to mist)
- safety valve set at 3 bar
- adjustable shoulder straps
- large handle for easy pumping

4 5 6 7 8

	Gachette 1L	F1 Viton®	Laser 2 Viton®	Exel 7	Exel 10
Usable volume (L)	1 L	0,6 L	1,5 L	5 L	8 L
Seals	Nitrile	Viton®	Viton®	Viton®	Viton®
Packaging (units per box)	48	50	6	12	8
Ref	100-100-871	100-002-519	100-002-136	100-003-765	100-003-766

- **100% repairable :** After-sales service based in France. 250 spare parts available for 10 years after purchase.
- Designed to withstand **agressive chemicals**
- Reliability and safety guaranteed by **ISO 9001 certification**

Laser 7

Pre-Pressurised Sprayers



JOINTS VITON SEALS



Wide Range of Aggressive and Acidic Chemical Products

- Professional lance handle with two-finger trigger, specially designed for acidic products
- Adjustable nozzle holder and 15/10e nozzle
- 110° flat fan nozzle
- 40 cm lance
- Translucent graduated tank with a wide opening for easy filling and complete emptying (no retention zones)
- Safety valve set at 3 bar
- Support knob for holding the tank during pumping, emptying, and filling

0 1 2 3 4 5 6 7 8 9 10

Laser 2 EPDM

Pre-Pressurised Sprayers



JOINTS EPDM SEALS



Neutral and Basic Products

Cleaning with disinfectants, vehicle shampoos, fungicides and animal repellents

- Handle with lock button for continuous spraying
- Translucent graduated tank with a wide opening for easy filling
- Anti-theft nozzle
- Safety valve set at 3 bar
- Adjustable nozzle (from straight jet to mist)

6 7 8 9 10

	Laser 7	Laser 2 EPDM
Usable volume (L)	5 L	1,5 L
Seals	Viton®	EPDM
Packaging (units per box)	1	6
Ref	100-003-752	100-002-137

Viton® est une marque de Dupont Dow Elastomers

17 avenue Jean Juif - CS 70015 - 51301 VITRY-LE-FRANÇOIS CEDEX - www.tricoflex.com
S.A.S.U. au Capital de 1 909 416 € - R.C.S. Châlons-en-Champagne 380 333 427
SIREN 380 333 427 - FR 60 380 333 427 - APE 2221 Z



Choice of seal type according to the pH of the sprayed products

JOINTS VITON SEALS	acidic products	0 1 2 3 4 5 6
JOINTS NITRILE SEALS	neutral products	6 7 8
JOINTS EPDM SEALS	basic products	8 9 10 11 12 13 14