



### Main

|                                    |                              |
|------------------------------------|------------------------------|
| Range of product                   | Modicon M171                 |
| Accessory / separate part category | Thermal management accessory |
| Accessory / separate part type     | Probe                        |
| Product specific application       | Temperature control          |

### Complementary

|                         |                                        |
|-------------------------|----------------------------------------|
| Temperature probe type  | NTC                                    |
| Mounting support        | Cables                                 |
| Cable length            | 5 M (+/- 3 %)                          |
| Electrical connection   | 2 conductors cable for controller side |
| Connections - terminals | Cable with wire end ferrule            |
| Fixing mode             | Clip-on                                |
| Width                   | 20 Mm                                  |
| Height                  | 6 Mm                                   |

### Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP68 |
|-------------------------|------|

### Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US1PC1222537  |
| Discount Schedule | PC12          |
| GTIN              | 3606480761768 |
| Returnability     | No            |
| Country of origin | IT            |

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 4.000 Cm  |
| Package 1 Width              | 10.500 Cm |
| Package 1 Length             | 4.500 Cm  |
| Package 1 Weight             | 58.000 G  |

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 4         |
| Package 2 Height             | 4.000 Cm  |
| Package 2 Width              | 10.500 Cm |
| Package 2 Length             | 15.000 Cm |
| Package 2 Weight             | 237.000 G |
| Unit Type of Package 3       | S01       |
| Number of Units in Package 3 | 36        |
| Package 3 Height             | 15.000 Cm |
| Package 3 Width              | 15.000 Cm |
| Package 3 Length             | 40.000 Cm |
| Package 3 Weight             | 2.300 Kg  |

### Offer Sustainability

|                                        |                                                                                                                                                 |
|----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65              | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is k                                                |
| REACH free of SVHC                     | Yes                                                                                                                                             |
| Toxic heavy metal free                 | Yes                                                                                                                                             |
| Mercury free                           | Yes                                                                                                                                             |
| Sustainable packaging                  | No                                                                                                                                              |
| Packaging made with recycled cardboard | Yes                                                                                                                                             |
| REACH Regulation                       | Free of Substances of Very High Concern above the threshold  |
| EU RoHS Directive                      | Compliant                                                      |
| Take-back                              | No                                                                                                                                              |

### Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|

Product Life Status : **Commercialised**