

KWD RANGE

KWD206 Zipper Safety Boot – S1P/S1



KING'S

by Honeywell

The Logical Choice



Description: Leather Side-zip Boot

Size: UK 3-13 | US 4-14 | EU 36-48

Application: Construction, Mining, Manufacturing, Heavy and General Industries, Utilities, Oil and Gas

Standard: SR (EN ISO 20345:2022); S1P/S1



| SKU | Steel Midsole | Color | Outsole | Category |
|---------|---------------|-------|-----------------|----------|
| KWD206 | Yes | Black | Dual Density PU | S1P |
| KWD206X | No | Black | Dual Density PU | S1 |

Features:

- Tough 2.0 - 2.2 mm thick full-grain leather upper with good breathability.
- Convenient, quick release side zip for easy donning and doffing.
- Padded ankle collar offers enhanced ankle comfort, support, and chafing prevention.
- Stability Torsion Zone offers optimal support for a wide range of foot arch profiles, helping to prevent feet pronation and supination.
- Exceptional shock absorption for elevated comfort and reduced feet fatigue.
- Outsole design engineered to complement the natural biomechanics of the walking gait.
- Wider outsole surface area provides increased contact with ground to enhance stability.
- Enhanced outsole thickness to deliver exceptional cushioning and comfort with every step.
- Strong leather upper and sole bond to withstand demanding work environments.
- Tread with deeper grip patterns and enhanced grip variations offers superior traction and stability.
- King's signature wide profile steel toecap for greater comfort.
- King's Comfort Footbed features ultra-breathable perforated channels for quick drying and all-day feet freshness.
- Highly breathable 3-D lining minimises skin abrasion, keeps feet insulated and effectively wicks away moisture.
- Lightweight, shock absorbing dual density polyurethane (PU) sole for added comfort.
- Wear-off indicators provide an early warning on sole wear and potential loss of grip.
- Excellent slip resistant sole delivers durable traction; SR (EN ISO 20345:2022); Anti-static.
- Sole resistant to mineral and organic oils.

SOLE FEATURES



Puncture Resistant



Anti-Static



Slip Resistant



Mineral Oils Resistant



Organic Oils & Fats Resistant

FOOTWEAR FEATURES



2.0 - 2.2mm Full Grain Leather



Wear-off Indicator



Toe Bumper



Steel Safety Toecap

COMFORT FEATURES



Wide Profile Toecap



Breathable Lining



Comfort Footbed



Impact Absorption



Lightweight



LEARN MORE
automation.honeywell.com

KWD206 | v11/24
© 2024 Honeywell International Inc.