



**129A-103-4**

**1/4"-1/2" Socket Hex Set Inch, 103 Pcs**






**PRODUCT DETAILS**

- 103 pcs socket set, AF sizes
- Bi-hex sockets, inch sizes
- Chrome vanadium alloy steel
- Chrome plated bright finish
- High density polyethylene box
- Box with metal latches
- Standards: DIN 3120, DIN 3124, DIN 3122



**PRODUCT ATTRIBUTES**

Product			
<b>129A-103-4</b>	103	80 x 280 x 380 mm	7000 g

## SET CONTENT



Hex Key Nickel Plated 1.5 mm  
**040001**



Hex Key Nickel Plated 2 mm - 5/64"  
**040011**



Hex Key Nickel Plated 2.5 mm  
**040021**



Socket 1/4" Hex 5/32"  
**101A-05-1**



Socket 1/4" Hex 3/16"  
**101A-06-1**



Socket 1/4" Hex 7/32"  
**101A-07-1**



Socket 1/4" Hex 1/4"  
**101A-08-1**



Socket 1/4" Hex 5/16"  
**101A-10-1**



Socket 1/4" Hex 11/32"  
**101A-11-1**



Socket 1/4" Hex 3/8"  
**101A-12-1**



Socket 1/4" Hex 7/16"  
**101A-14-1**



Socket 1/4" Hex 1/2"  
**101A-16-1**



Socket 1/4" Hex 9/16"  
**101A-18-1**



Extension 1/4" 50 mm  
**105-22-1**



Extension 1/4" 100 mm  
105-24-1



Universal Joint 1/4"  
105-40-1



Sliding T-Handle 1/4"  
105-42-1



Spinner Handle 1/4"  
105-50-1



Ratchet 1/4" Pear Type, 72 Teeth,  
150 mm  
105-70-1



Socket 1/4" Torx E-4  
106-04-1



Socket 1/4" Torx E-5  
106-05-1



Socket 1/4" Torx E-6  
106-06-1



Socket 1/4" Torx E-7  
106-07-1



Socket 1/4" Torx E-8  
106-08-1



Phillips Bit Socket 1/4" PH1  
107-PH1-1



Phillips Bit Socket 1/4" PH2  
107-PH2-1



Pozidriv Bit Socket 1/4" PZ1  
107-PZ1-1



Pozidriv Bit Socket 1/4" PZ2  
107-PZ2-1



Torx Bit Socket 1/4" T8  
107-T08-1



Torx Bit Socket 1/4" T10  
107-T10-1



**Torx Bit Socket 1/4\" T15**  
**107-T15-1**



**Torx Bit Socket 1/4\" T20**  
**107-T20-1**



**Torx Bit Socket 1/4\" T25**  
**107-T25-1**



**Torx Bit Socket 1/4\" T27**  
**107-T27-1**



**Torx Bit Socket 1/4\" T30**  
**107-T30-1**



**Slotted Bit Socket 1/4\" 0.8x4**  
**107-0840-1**



**Slotted Bit Socket 1/4\" 1x5.5**  
**107-1055-1**



**Slotted Bit Socket 1/4\" 1.2x8**  
**107-1280-1**



**Socket 1/2\" Bihex 3/8\"**  
**122A-12-1**



**Socket 1/2\" Bihex 7/16\"**  
**122A-14-1**



**Socket 1/2\" Bihex 1/2\"**  
**122A-16-1**



**Socket 1/2\" Bihex 9/16\"**  
**122A-18-1**



**Socket 1/2\" Bihex 5/8\"**  
**122A-20-1**



**Socket 1/2\" Bihex 11/16\"**  
**122A-22-1**



**Socket 1/2\" Bihex 3/4\"**  
**122A-24-1**



**Socket 1/2\" Bihex 13/16\"**  
**122A-26-1**



Socket 1/2" Bihex 7/8"  
122A-28-1



Socket 1/2" Bihex 15/16"  
122A-30-1



Socket 1/2" Bihex 1.1/16"  
122A-34-1



Socket 1/2" Bihex 1.3/16"  
122A-38-1



Socket 1/2" Bihex 1.1/4"  
122A-40-1



Extension 1/2" 125 mm  
125-23-1



Extension 1/2" 250 mm  
125-25-1



Universal Joint 1/2"  
125-40-1



Sliding T-Handle Head 1/2"  
125-43-1



Bit Holder 1/2" to Hex 5/16"  
125-48-1



Spark Plug 1/2" Size 5/8"  
125-53-1



Spark Plug 1/2" Size 13/16"  
125-54-1



Ratchet 1/2" Pear Type, 72 Teeth,  
250 mm  
125-70-1



5/16" Bit Hex 10, 2 Pcs  
470-H10-1



5/16" Bit Hex 7, 2 Pcs  
470-H7-1



5/16" Bit Hex 8, 2 Pcs  
470-H8-1



5/16" Bit PH3, 2 Pcs  
470-PH3-1



5/16" Bit PH4, 2 Pcs  
470-PH4-1



5/16" Bit Torx 40, 2 Pcs  
470-T40-1



5/16" Bit Torx 45, 2 Pcs  
470-T45-1



5/16" Bit Torx 50, 2 Pcs  
470-T50-1



5/16" Bit Torx 55, 2 Pcs  
470-T55-1



5/16" Bit Slotted 10, 2 Pcs  
470-10.0-1



5/16" Bit Slotted 12, 2 Pcs  
470-12.0-1



5/16" Bit Slotted 8.0, 2 Pcs  
470-8.0-1



Socket 1/4" Deep Hex 3/16"  
103A-06-1



Socket 1/4" Deep Hex 1/4"  
103A-08-1



Socket 1/4" Deep Hex 9/32"  
103A-09-1



Socket 1/4" Deep Hex 5/16"  
103A-10-1



Socket 1/4" Deep Hex 11/32"  
103A-11-1



Socket 1/4" Deep Hex 3/8"  
103A-12-1



Socket 1/4" Deep Hex 7/16"  
103A-14-1



Socket 1/4" Deep Hex 1/2"  
103A-16-1



Hex Bit Socket 1/4" - 1/8"  
107A-4-1



Hex Bit Socket 1/4" - 5/32"  
107A-5-1



Hex Bit Socket 1/4" - 3/16"  
107A-6-1



Hex Bit Socket 1/4" - 7/32"  
107A-7-1



Socket 1/2" Bihex 5/16"  
122A-10-1



Socket 1/2" Bihex 11/32"  
122A-11-1



Socket 1/2" Deep Bihex 9/16"  
124A-18-1



Socket 1/2" Deep Bihex 5/8"  
124A-20-1



Socket 1/2" Deep Bihex 11/16"  
124A-22-1



Socket 1/2" Deep Bihex 3/4"  
124A-24-1



Socket 1/2" Deep Bihex 13/16"  
124A-26-1



Socket 1/2" Torx E-10  
126-10-1



Socket 1/2" Torx E-11  
126-11-1



Socket 1/2" Torx E-12  
126-12-1



Socket 1/2" Torx E-14  
126-14-1



Socket 1/2" Torx E-16  
126-16-1



Socket 1/2" Torx E-18  
126-18-1



Socket 1/2" Torx E-20  
126-20-1



Socket 1/2" Torx E-24  
126-24-1