

A-INSP-PG21-65N-P-BK - Screw plug



1415214

<https://www.phoenixcontact.com/gb/products/1415214>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw plug, material for screw connection: PA, connecting thread: Pg21, color: jet black RAL 9005, with O-ring



Commercial data

Item number	1415214
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 703 (C-2-2019)
GTIN	4055626038575
Weight per piece (including packing)	4.81 g
Weight per piece (excluding packing)	4.77 g
Customs tariff number	39269097
Country of origin	DE

A-INSP-PG21-65N-P-BK - Screw plug



1415214

<https://www.phoenixcontact.com/gb/products/1415214>

Technical data

Product properties

Product type	Plug for cable screw gland
--------------	----------------------------

Dimensions

Dimensional drawing	
Length	11 mm
Length of the connecting thread	8 mm
Diameter	28.3 mm
	33 mm
Connecting thread diameter	28.3 mm
Hexagon angular dimension	Diameter
Thread type connection side	Pg21

Material specifications

Material	PA
Seal material Flat gasket	EPDM
Material for screw connection	PA

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 100 °C


A-INSP-PG21-65N-P-BK - Screw plug

1415214


<https://www.phoenixcontact.com/gb/products/1415214>

Drawings

Dimensional drawing



Dimensional drawing



A-INSP-PG21-65N-P-BK - Screw plug



1415214

<https://www.phoenixcontact.com/gb/products/1415214>

Classifications

ECLASS

ECLASS-13.0	23111190
-------------	----------

ETIM

ETIM 9.0	EC000032
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

A-INSP-PG21-65N-P-BK - Screw plug



1415214
<https://www.phoenixcontact.com/gb/products/1415214>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk