




PE terminal 1 screw terminal green-yellow, 7.2mm, Sz. 4



Model	
product brand name	ALPHA
product designation	PE through-type terminal
General technical data	
insulation material	thermoplastic
terminal contact spacing	7.2 mm
Protection class	
combustibility class according to UL 94	V2
Appearance	
color	green-yellow
Product details	
product component required end cover plate	No
Number	
number of terminal levels	1
number of terminal points per terminal level	1
Connections	
stripped length	11 mm
connectable conductor cross-section solid	
• maximum	4 mm²
connectable conductor cross-section stranded	
• maximum	4 mm²
connectable conductor cross-section finely stranded	
• with core end processing maximum	4 mm²
• without core end processing maximum	4 mm²
tightening torque with screw-type terminals	
• minimum	0.5 N·m
• maximum	0.5 N·m
type of connection 1	screw-type terminal
type of connection 2	screw-type terminal
position of the terminal	lateral
Mechanical Design	
height with lowest-profile installation	30 mm
length	51 mm
fastening method	DIN rail 35 mm
net weight	22.4 g
material of the insulating body	Thermoplastic
Environmental conditions	
ambient temperature during operation	
• minimum	-25 °C
• maximum	55 °C

Approvals Certificates

General Product Approval	Declaration of Con- formity	other	Environment	
Confirmation	  EG-Konf.	Confirmation	Miscellaneous	Environmental Con- firmations

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WA1011-1PG01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WA1011-1PG01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WA1011-1PG01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

10/6/2021 

