

## Plug-in card block - SKBI 64/G64 - 2263117


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug-in card block, Nominal current: 4 A, Number of positions: 64, Pitch: 5.08 mm, Connection method: Screw connection



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 053895
Weight per Piece (excluding packing)	314.2 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Length	66 mm
Height	162 mm
Width	118 mm
Pitch	5.08 mm
Hole diameter	4.2 mm

#### General

Range of articles	SKBI 64
Connection in acc. with standard	EN-VDE
Nominal current $I_N$	4 A
Nominal voltage $U_N$	250 V (in acc. with DIN VDE 0110/Gr.B)
Nominal cross section	2.5 mm <sup>2</sup>
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm
Number of positions	64

# Plug-in card block - SKBI 64/G64 - 2263117

## Technical data

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260710
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002642
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

### Approvals

### GOST / GOST

---

### Ex Approvals



---

# Plug-in card block - SKBI 64/G64 - 2263117

## Approvals

Approvals submitted

## Approval details



## Accessories


### Accessories

Accessories - SF-SKBI 64 - 2263007

Snap foot, for horizontal or vertical mounting of the SKBI plug-in card blocks, on the NS 35/7.5 DIN rail

## Drawings

Dimensioned drawing



Schematic diagram

