

Part Number : [1731121920](#)
Product Description : FCT EasyLock Latch Screw,
M3 Thread, Stainless Steel, 19.70mm Length,
0.80-1.30mm Panel Thickness
Series Number : 173112
Status : Active
Product Category : D-Sub Accessories
Engineering Part Number : F-SRH/01M3-6373



Documents and Resources

Drawings

[1731121920_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	D-Sub Accessories
Series	173112
Description	FCT EasyLock Latch Screw, M3 Thread, Stainless Steel, 19.70mm Length, 0.80-1.30mm Panel Thickness
IP Rating	N/A
Magnetic	Yes
Product Name	EasyLock
Type	Backshell
UPC	198930886334

Physical

Accessory Type	Latch Screw
Material - Body	Stainless Steel
Packaging Type	Bag
Thread Size	M3
Thread Type	Standard

Mates With / Use With

Use with Part(s)

Description	Part Number
FCT EasyLock Plastic Backshell for D-Sub Connector, Black, Shell Size 1, Push-Pull Locking, Straight or Side Cable Outlet	<u>1731110948</u>
FCT EasyLock Plastic Backshell for D-Sub Connector, Black, Shell Size 2, Push-Pull Locking, Straight or Side Cable Outlet	<u>1731110949</u>

FCT EasyLock Plastic Backshell for D-Sub Connector, Black, Shell Size 3, Push-Pull Locking, Straight or Side Cable Outlet	<u>1731110950</u>
FCT EasyLock Plastic Backshell for D-Sub Connector, Shielded, Shell Size 1, Push-Pull Locking, Straight or Side Cable Outlet	<u>1731110951</u>
FCT EasyLock Plastic Backshell for D-Sub Connector, Shielded, Shell Size 2, Push-Pull Locking, Straight or Side Cable Outlet	<u>1731110952</u>
FCT EasyLock Plastic Backshell for D-Sub Connector, Shielded, Shell Size 3, Push-Pull Locking, Straight or Side Cable Outlet	<u>1731110953</u>