

Previously known as: MICROGARD® 1800 Ts PLUS - Model 111

Lightweight, breathable full-body protection suit, featuring microporous laminate technology.

- **Specialized protection:** Made from microporous laminate material, the AlphaTec® 1800 Ts PLUS Stitched & Taped - Model 111 protects against particulates and low-hazard liquid spray*
- **Heightened breathability:** This microporous laminate fabric is permeable to air and water vapor, reducing the risk of heat stress
- **Reduced contamination risks:** As it is low-linting in nature, the risk of cross contamination in critical areas is also minimized
- **Enhanced fit and features:** An optimized fit means personal protection in optimal comfort, with stitched and taped seams enhancing this protective suit's strength further and elastics boosting wearer comfort
- **Decreased surface defect risks:** This protective outer garment's silicone-free construction also makes it appropriate for spray-painting applications
- **Assured antistatic properties:** In addition, it has been tested against EN 1149-5 and AATCC 76 standards

*this chemical-protective suit ensures CE Category III Type 4/5/6 protection



Industries

- Life Sciences
- Automotive
- Metal fabrication
- Food Processing
- Chemical
- Automotive Aftermarket
- Nuclear

Applications

- Clean room cleaning and preparing
- Body painting including surface inspection
- Production line support & maintenance
- Cleaning of plant and machines
- Maintenance of plant and machines
- Fibre Glass Resin Applications
- Handling of powders


KEY FEATURES & BENEFITS

- **Microporous laminate fabric:** Resistance to particulates and low-hazard spray
- **Air and water vapor permeability:** Reduced heat stress, increased comfort
- **Low-linting material:** Lower risk of cross contamination in critical zones

Material Diagram



Seam Diagram



Performance Standards



0598EN 1073-2EN 1149-5EN 14126EN ISO 13688:2013

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL, 4XL, 5XL
Color	White
Country Of Origin	China
Models Available	122, 156
Packaging Overview	Individually Packed
Product Material	Microporous polyethylene Laminate non-woven
Product Reference	1800 Ts PLUS - Model 111
Standards Overview	CE CATEGORY III (Type 4-B, Type 5-B, Type 6-B, EN 1073-2, EN 14126, EN 1149-5)
Seam Type	Stitched and Taped
Shelf Life	5 years
Style Number	W18T111

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall, 3-piece hood, single zipper with re-sealable storm flap, finger loops and chin strap. Tunnelled elasticated wrists, hood and ankles.

For additional in formation visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

