

## General Information

|                               |  |
|-------------------------------|--|
| <b>Extended Product Type:</b> | SCH6   |
| <b>Product ID:</b>            | 1SNA199393R2200                                  |
| <b>EAN:</b>                   | 3472591993936                                    |
| <b>Catalog Description:</b>   | SCH6 Circuit Separators Beige                    |
| <b>Long Description:</b>      | SCH6 - Circuit Separators - Beige - 4mm Spacing. |

## Additional Information

|   |  |
|---|--|
| <b>ABB Industrial IT Suite:</b>           | Control IT   |
| <b>Ambient Air Temperature:</b>           | Operation -55 ... +110 °C  |
| <b>Color:</b>                             | Beige  |
| <b>Country of Origin:</b>                 | France (FR)  |
| <b>Customs Tariff Number:</b>             | 39269097   |
| <b>EAN:</b>                               | 3472591993936  |
| <b>ETIM 4:</b>                            | EC000886 - Endplate and partition plate for terminal block   |
| <b>ETIM 5:</b>                            | EC000886 - Endplate and partition plate for terminal block   |
| <b>ETIM 6:</b>                            | EC000886 - Endplate and partition plate for terminal block   |
| <b>Environmental Information:</b>         | 1SND220090E1000  |
| <b>Function:</b>                          | Circuit Separators   |
| <b>IIT Publishing Status:</b>             | Level 0 - Information enabled  |
| <b>Industrial IT Certification Level:</b> | 0  |
| <b>Insulation Material:</b>               | Polyamide  |
| <b>Invoice Description:</b>               | SCH6 Circuit Separators Beige  |
| <b>Minimum Order Quantity:</b>            | 20 piece   |
| <b>Mounting on DIN Rail:</b>              | Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461<br>TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715<br>TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| <b>Object Classification Code:</b>        | X  |
| <b>Order Multiple:</b>                    | 20 piece   |
| <b>Package Level 1 EAN:</b>               | 3472591993936  |
| <b>Package Level 1 Gross Weight:</b>      | 1.896 kg   |
| <b>Package Level 1 Units:</b>             | 20 piece   |
| <b>Product Main Type:</b>                 | SCH  |
| <b>Product Name:</b>                      | Separator  |
| <b>Product Net Depth:</b>                 | 65 mm  |
| <b>Product Net Height:</b>                | 39.5 mm  |
| <b>Product Net Weight:</b>                | 94.8 g   |
| <b>Product Net Width:</b>                 | 4 mm   |
| <b>Selling Unit of Measure:</b>           | piece  |
| <b>Spacing:</b>                           | 4 mm   |
| <b>Suitable For:</b>                      | HD16/14.FF5  |

