


K 2 Compact



Compact and lightweight, the K2 Compact pressure washer is easy to transport, making it ideal for all cleaning tasks around the home. This portable pressure washer includes a trigger gun, a 4m high pressure hose, one way lance, detergent suction facility and a dirtblaster lance. The dirtblaster lance provides up to 50% greater cleaning power than a standard high pressure lance, making it the perfect patio pressure washer. With an ergonomically designed trigger gun, the pressure switch control switches the motor on and off, while the impact-resistant, recyclable plastic casing prevents dirt particles from damaging the motor and pump. Pressure washing with any Kärcher K2 compact pressure washer can be achieved by using a gravity fed harvested water source such as a water butt tap. The K2 Compact portable pressure washer also comes with a 2 year guarantee.





K 2 Compact

Technical data

Order No.		1.673-122.0
EAN code		4039784720206
Pressure	bar / MPa	~110 / ~11
Flow rate	l/h	360
Max. water feed temperature	°C	40
Power rating	kW	1,4
Weight without accessories	kg	4
Dimensions (L x W x H)	mm	280 x 176 x 443
Area performance	m²/h	20

Equipment

Integrated mesh water filter		■
Adapter garden hose A3/4"		■
High-pressure hose	m	4
One-way spray lance		■
		–
Dirt Blaster		■

■ Included in delivery.

Accessories for K 2 Compact 1.673-122.0



		Order No.						Price	Description	
Spray lances										
DB 145 Dirt Blaster	1	2.643-244.0							Dirt blaster with powerful rotating nozzle ideal for removing stubborn dirt. Ideal for moss covered or weathered surfaces. For use with K2 - K4 Machines.	■
VP 120 Vario Power Jet	2	2.643-241.0							Vario-Power spray lance: spray lance with variable pressure control from low-pressure detergent jet to high-pressure jet. For use with K2 Machines.	■
Splash guard for dirt blaster	3	2.640-916.0							Splash guard for dirt blasterProtects against splash back when cleaning corners and edges. Fits all Kärcher dirt blasters (except 4.763-184).	□
Angled spray lance	4	2.638-817.0							Extra-long angled spray lance (about 1 m) for easy cleaning of difficult to reach areas, e.g. roof gutters or vehicle underbodies.	□
Single Lance Extension	5	2.643-240.0							Extends spray lance by 0.5 m. For effective cleaning of difficult to reach areas. Suitable for all Kärcher accessories.	□
3-stage lance extension	6	2.639-722.0							3-stage lance extension set with four aluminium lances for difficult to reach areas. Variable extension to 90 cm, 1.30 m and 1.70 m.	□
Telescopic jet pipe	7	2.642-347.0							The Kärcher Telescopic jet pipe allows for easy cleaning of difficult to reach areas. With a shoulder strap and an ergonomically adjustable trigger gun, allowing you to reach up to 4m.	□
VP 145 Vario Power Jet	8	2.643-253.0							The Kärcher short Vario Power nozzle comes with pressure regulation and is adjustable 360°, making it ideal for cleaning difficult to reach areas. For use with K2 - K4 Machines.	□
Miscellaneous										
Replacement gun model "Good"	9	2.641-959.0							Replacement gun for Kärcher K2 – K7 series domestic pressure washers. For all pressure washers where the hose is secured to the gun with a clip (without Quick Connect).	■
Water filter	10	4.730-059.0							Water filter protects pressure washer pumps against dirt particles from dirty water.	□
Replacement O-ring set	11	2.640-729.0								□
Pistol best 2K Packed	12	2.642-172.0								□
Adapter for garden hose connection	13	2.640-732.0								□
Hard surface cleaners										
PS40 Power Scrubber Surface Cleaner	14	2.643-245.0							The Kärcher PS40 power scrubber comes with three integrated high-pressure nozzles giving you a powerful, reliable and time-saving solution for removing stubborn dirt on a variety of surfaces.	□
T 300 "T-Racer" surface and patio cleaner	15	2.640-212.0							T 300 T-Racer. For cleaning flat surfaces without splash back. Additional handle for vertical surfaces. Features two rotating flat jet nozzles. Hovercraft effect. Distance of nozzle to surface adjustable.	□
T-Racer replacement nozzles, grey, K2 – K5	16	2.640-727.0							High-quality, grey replacement nozzles for T-Racer nozzles. Suitable for nozzle replacement for K2 – K5 series (T 250, T 300, T 400).	□
T350 Patio Cleaner	17	2.643-252.0							The Kärcher T350 patio cleaner allows you to clean large areas quickly and efficiently, as well as being splash-free. This model includes adjustable cleaning pressure for different surfaces.	□
Spare nozzles accesories	18	2.643-338.0								□
Spare nozzles accesories T 300 / T 350	19	2.643-335.0								□
T 250 plus	20	2.642-194.0								□

■ Included in delivery. □ Available accessories.

Accessories for K 2 Compact 1.673-122.0



		Order No.						Price	Description	
Brushes										
WB150 Power Brush	21	2.643-237.0							The Kärcher WB150 power brush allows for splash-free cleaning of sensitive surfaces. Its efficient combination of high pressure and manual brush pressure saves energy, water and 30% time.	☐
WB60 Soft Surface Wash Brush	22	2.643-233.0							The Kärcher WB60 soft wash brush is a great addition to your Kärcher pressure washer to help you clean larger surfaces like cars, caravans, boats and conservatories.	☐
WB100 Rotating Wash Brush	23	2.643-236.0							The Kärcher WB100 rotating wash brush is ideal for cleaning all smooth surfaces like paint, glass or plastic. It comes with a 180° joint making it infinitely adjustable.	☐
Wheel Washing Brush	24	2.643-234.0							The Kärcher wheel washing brush is perfect for removing dirt and grime that accumulates on your wheel rims. With 360° degree cleaning enabling you to reach every angle of your wheels.	☐
WB50 Soft Wash Brush	25	2.643-246.0							The Kärcher WB50 soft wash brush is suitable for thorough cleaning on all surfaces. With soft bristles that are gentle on all types of surfaces.	☐
Standard wash brush	26	6.903-276.0							Slim brush for cleaning stubborn dirt	☐
High-pressure hose extension - System up to 2007										
High-pressure extension hose, 10 m, K2 - K7	27	6.389-092.0							High-pressure extension hose for greater flexibility, 10 m robust DN 8 quality hose. Textile braiding reinforced, non-kinking hose with brass connector for durability.	☐
	28	6.390-961.0								☐
High-pressure extension rubber hose, 10 m, K2 - K8.	29	6.390-096.0							High-pressure extension rubber hose for greater flexibility. 10 m high-quality rubber hose, steel reinforced for durability. Temperature: up to 80 °C. Pressure: up to 160 bar.	☐
Special applications										
Pipe cleaning set, 7.5 m	30	2.637-729.0							Pipe cleaning set with 7.5 m hose for clearing blockages in pipes, drains, downpipes and toilets.	☐
Pipe cleaning set, 15 m	31	2.637-767.0							Pipe cleaning set with 15 m hose for clearing blockages in pipes, drains, downpipes and toilets.	☐
Sand/wet blasting set	32	2.638-792.0							Sand and wet blasting set for removing rust, paint and stubborn dirt using Kärcher abrasive.	☐
Vario joint	33	2.640-733.0							Vario joint, rotates 180° for cleaning difficult to reach areas. Connection: For connection between gun and accessory or extension lance and accessory.	☐
Foam nozzle FJ 6	34	2.643-147.0							The Kärcher FJ6 foam nozzle is the perfect addition to your Kärcher pressure washer, allowing you to add a layer of foamy detergent with the minimum of effort and fuss.	☐
Foam nozzle Connect 'n' Clean FJ10 C Ultra Foam Cleaner 1L	35	2.643-143.0							The Kärcher Ultra Foam Detergent & FJ10 C Connect 'n' Clean foam nozzle is the most effective way to apply detergent. Allowing you to switch between detergents for different tasks.	☐
FJ 10 C Connect 'n' Clean Foam and Care nozzle with Car Shampoo	36	2.643-144.0							Car Shampoo & FJ 10 C Connect 'n' Clean foam nozzle - The most effective way to apply detergent. Also allows a simple switch between different detergents for different tasks.	☐
FJ 10 C Connect 'n' Clean Foam and Care nozzle with Stone Cleaner	37	2.643-145.0							3in1 Stone cleaner & FJ 10 C Connect 'n' Clean foam nozzle - The most effective way to apply detergent. Also allows a simple switch between different detergents for different tasks.	☐
Roof gutter and pipe cleaning set	38	2.642-240.0							The Kärcher roof gutter and pipe cleaning kit is an effective way to clean and remove blockages in pipes, drains, downpipes and toilets. Compatible with all Kärcher pressure washers.	☐

■ Included in delivery. □ Available accessories.

Accessories for K 2 Compact 1.673-122.0



39



40



41



42



43



44



45



46

		Order No.						Price	Description	
Accessory kits										
Accessory Kit Bike Cleaning	39	2.643-551.0								☐
Accessory Kit Car Cleaning	40	2.643-554.0								☐
Accessory Kit Wood Cleaning	41	2.643-553.0								☐
High-pressure hose extension - System from 2009										
High-pressure replacement hose, 9 m, K3 - K7	42	2.641-721.0							9 m high-pressure replacement hose for K3 – K7 series domestic pressure washers from 2009, where the hose is connected to the gun and pressure washer per Quick Connect connector, 160 bar, 60 °C.	☐
High-pressure hose replacement kit - from 1992										
H 12 High Pressure Hose	43	2.642-953.0								☐
Quick Connect accessory set	44	2.641-828.0								☐
Adapter Set Extension Hose	45	2.643-037.0								☐
Accessories kit quick connect *UK	46	2.642-301.0								☐

■ Included in delivery. □ Available accessories.

Accessories for K 2 Compact 1.673-122.0



		Order No.						Price	Description	
Connectors/Tap adaptors										
Universal hose coupling	1	2.645-191.0	–							☐
Hoses & Hose Reels/Trolleys										
Connection Set for high-pressure cleaners	2	2.645-156.0	–							☐
	3	2.645-258.0	–							☐
PrimoFlex® hose 1/2" – 20 m	4	2.645-138.0	–							☐
Hose Trolley HT 3.420 Kit 5/8"	5	2.645-167.0	–							☐
Premium Hose Reel HR 7.315 Kit 1/2"	6	2.645-164.0	–							☐

■ Included in delivery. □ Available accessories.