

Product data sheet

Specifications

Repacked, comb busbar, Acti9, 80A, 3L+N, 48 modules, 9mm pitch, mcb with aux



A9XPA748W



This repacked option saves 4.543 over the standard condition

Main

Range	Acti9
Product or component type	Comb busbar
Mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	48
Standards	EN/IEC 60439-1

Complementary

Number of ways	32 ways Aux + N + L
Distribution type	Aux N L1 Aux N L2 Aux N L3
Poles configuration for 1 way	1 x 1P + N
Connection pitch	9 mm between phase and neutral
Connector type	Tooth
Distance between way	27 mm
Marking	N L1 N L2 N L3
Insulation	Insulated
Device presentation	Cuttable
Provided equipment	end-pieces tooth covers
[Ie] rated operational current	80 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N
[Ui] rated insulation voltage	400 V AC conforming to IEC 61439-1
[Uimp] rated impulse withstand voltage	4 kV
Mounting location	Top on tunnel type terminals
9 mm pitches	96
Height	29 mm
Width	862 mm
Depth	26 mm
Product weight	521 g
Colour	White (RAL 9003)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Range compatibility	Acti9 C40 Acti 9 C40 Vigi Acti 9 DT40 Acti 9 DT40 Vigi Acti 9 iDPN Acti 9 iDPN Vigi Multi9 N40 Acti9 iC40 Acti9 iDT40 Acti9 Acti9 iDD40 Acti9 Acti9 iDD40 TG Acti9 Vigi iTG40 Acti9 iLG40 Acti9 iCV40 Acti9 Vigi iCG40 Acti9 iID40
---------------------	---

Environment

Fire resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution degree	3 conforming to EN/IEC 60439-1
IP degree of protection	IP20 with end-pieces and tooth covers

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.9 cm
Package 1 Width	2.9 cm
Package 1 Length	86.2 cm
Package 1 Weight	518 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6.4 cm
Package 2 Width	8.5 cm
Package 2 Length	89.6 cm
Package 2 Weight	2.714 kg
Unit Type of Package 3	P12
Number of Units in Package 3	200
Package 3 Height	45 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	120.52 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

12618b2a-bc0e-4c2d-bb7b-9185c26e01fe

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins