

AI-WM 1,5-8 WH - Ferrule

3240545

<https://www.phoenixcontact.com/gb/products/3240545>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule with insulating collar that can be labeled. When using the magazine, the ferrules can be labeled with BLUEMARK.



Your advantages

- Electrogalvanized
- Ferrules made from electrolytic copper
- Highly resistant and optimum printing quality thanks to modern UV printing technology
- Crimping and marking in one step
- Ferrules can be labeled with BLUEMARK

Commercial data

Item number	3240545
Packing unit	780 pc
Minimum order quantity	780 pc
Sales key	BH3415
Product key	BH3415
Catalog page	Page 201 (C-3-2019)
GTIN	4046356547772
Weight per piece (including packing)	0.26 g
Weight per piece (excluding packing)	0.25 g
Customs tariff number	85369010
Country of origin	DE

AI-WM 1,5-8 WH - Ferrule

3240545

<https://www.phoenixcontact.com/gb/products/3240545>




Technical data

Product properties

Product type	Cable end sleeve
--------------	------------------

Dimensions

Dimensional drawing	
Width	4.6 mm
Sleeve length	8 mm
Ferrule diameter	2.1 mm
Sleeve wall thickness	0.15 mm
Inner dimensions of the insulating collar	3.4 mm

Internal dimensions

Internal diameter	1.8 mm
-------------------	--------

Material specifications

Color	white (RAL 9010)
Material	E-CU
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Cable/line

External cable diameter	= 1.50 mm
-------------------------	-----------

Mechanical properties

Technical data

Sleeve length	8 mm
---------------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

Al-WM 1,5-8 WH - Ferrule


3240545

<https://www.phoenixcontact.com/gb/products/3240545>



Drawings

Dimensional drawing



AI-WM 1,5-8 WH - Ferrule



3240545

<https://www.phoenixcontact.com/gb/products/3240545>

Classifications

ECLASS

ECLASS-13.0	27400201
-------------	----------

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI-WM 1,5-8 WH - Ferrule



3240545
<https://www.phoenixcontact.com/gb/products/3240545>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk